



- 1 Type**
Operation with
DK triangular spindle (DK7)
VK7 square spindle A/F7
VK8 square spindle A/F8

Metric table

2

Dimensions in: millimeters - inches

Latch distance A														
4	6	8	10	13	14	16	18	20	22	24	26	28	30	32
0.16	0.24	0.31	0.39	0.51	0.55	0.63	0.71	0.79	0.87	0.94	1.02	1.10	1.18	1.26

Specification

3

- Cam latch housing
Zinc die-cast
- Locating ring
Powder coated
Black, RAL 9005, textured finish **● SW**
- Latch arm / assembly hardware
Steel, zinc plated, blue passivated finish
- **RoHS compliant**

Accessory

- Socket keys GN 119.2
- Protective caps GN 120
- Opening handles GN 120.1

Information

GN 115.9 safety cam latches have a **push-to-turn** safety function. In the two end positions the spindle is locked in place by the latch arm. The latch arm can be turned 90° (a quarter of a turn) only when the operating element / key is pushed in, which releases the safety pin from the locked position. This feature protects the latch arm from moving on its own or as the result of vibrations.

The beveled edges of the latch arm create a smooth latching of the door. The 15 different off-set latch arm options allow the "Latch Distance A" to be set between 4 mm and 32 mm.

Product comes supplied with a loosely enclosed latch arm.

The socket key latches the latch arm and provides security from accidentally opening but does not lock the arm in place.

A socket key is not included.

see also...

- *Construction and Assembly Instructions*
- *List of Cam Latch Types*
- *Protective Guide Plates GN 120.2*

How to order

GN 115.9-DK-32-SW

1	Type
2	Latch distance A
3	Finish (Locating ring)