



Metric table

2

Dimensions in: millimeters - inches

Latch distance A														d	h
6	10	14	18	20	22	24	26	28	30	34	38	40	50	28	4
0.24	0.39	0.55	0.71	0.79	0.87	0.94	1.02	1.10	1.18	1.34	1.50	1.57	1.97	1.10	0.16

Specification3

• Cam lock housing

Stainless steel AISI 303

NI

• Latch arm

Stainless steel AISI 304

• Key

Nickel silver with plastic hand piece

• Stainless Steel Characteristics → page 2143

• RoHS compliant

Accessory

• Protective caps GN 120

→ www.jwwinco.com

• Opening handles GN 120.1

→ www.jwwinco.com

• Protective guide plates GN 120.2

→ www.jwwinco.com

Information

GN 115 stainless steel cam locks lock by a turning operation limited to 90° (quarter of a turn), which moves the latch arm behind the door frame. The beveled edges of the latch arm create a smooth latching of the door.

The 14 different off-set latch arm options allow for “Latch Distance A” to be set between 6 mm and 50 mm.

Two keys are supplied with each cam lock. They are keyed alike and can be operated with the identical key. The key may be inserted or withdrawn in both the locked and unlocked positions.

Product comes supplied with a loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → page 1261
- List of Cam Latch / Cam Lock Types → page 1256
- Cam Latches GN 115 (Stainless Steel, with Operating Elements) → page 1266
- Cam Latches GN 115 (Stainless Steel, Operation with Socket Key) → page 1266
- Cam Locks GN 115 (Zinc Die-Cast) → page 1263

How to order	1	Type
GN 115-SC-40-NI	2	Latch distance A
	3	Material