

1					1 Dimensions in: millimeters - <i>inches</i>				
l₁	a₃	a₄	a₅	a₆	l₁	a₃	a₄	a₅	a₆
400 <i>15.75</i>	288 <i>11.34</i>	320 <i>12.60</i>	-	-	700 <i>27.56</i>	448 <i>17.64</i>	480 <i>18.90</i>	-	-
450 <i>17.72</i>	288 <i>11.34</i>	320 <i>12.60</i>	-	-	800 <i>31.50</i>	384 <i>15.12</i>	416 <i>16.38</i>	672 <i>26.46</i>	704 <i>27.72</i>
500 <i>19.69</i>	352 <i>13.86</i>	384 <i>15.12</i>	-	-	900 <i>35.43</i>	416 <i>16.38</i>	448 <i>17.64</i>	768 <i>30.24</i>	800 <i>31.50</i>
550 <i>21.65</i>	352 <i>13.86</i>	384 <i>15.12</i>	-	-	1000 <i>39.37</i>	480 <i>18.90</i>	512 <i>20.16</i>	864 <i>34.02</i>	896 <i>35.28</i>
600 <i>23.62</i>	448 <i>17.64</i>	480 <i>18.90</i>	-	-	1200 <i>47.24</i>	576 <i>22.68</i>	608 <i>23.94</i>	1056 <i>41.57</i>	1088 <i>42.83</i>

1							Dimensions in: millimeters - <i>inches</i>						
i ₁	i ₁	i ₂	i ₃	i ₄	i ₅	i ₆	i ₁	i ₁	i ₂	i ₃	i ₄	i ₅	i ₆
400 15.75	43 1.69	118 4.65	193 7.60	268 10.55	343 13.50	-	700 27.56	43 1.69	193 7.60	343 13.50	493 19.41	643 25.31	-
450 17.72	43 1.69	130.5 5.14	218 8.58	305.5 12.03	393 15.47	-	800 31.50	20 0.79	271 10.67	522.5 20.57	774 30.47	-	-
500 19.69	43 1.69	143 5.63	243 9.57	343 13.50	443 17.44	-	900 35.43	20 0.79	305 12.01	589 23.19	874 34.41	-	-
550 21.65	43 1.69	155.5 6.12	268 10.55	380.5 14.98	493 19.41	-	1000 39.37	20 0.79	258.5 10.18	497 19.57	735.5 28.96	974 38.35	-
600 23.62	43 1.69	168 6.61	293 11.54	418 16.46	543 21.38	-	1200 47.24	20 0.79	251 9.88	482 18.98	712 28.03	943 37.13	1174 46.22

For the listed loading forces F_S to be absorbed reliably in the surrounding structure, all available countersunk holes of the outer and inner slide must be used. Failure to use mounting screws reduces the specified load capacity accordingly. The following screws can be used for mounting:

Designation - Standard		Outer slide	Inner slide
Phillips countersunk flat head screw	DIN 965	M 5	M 4
Phillips countersunk flat head self-tapping screw	DIN 7997	Size 5	Size 4 / 4.5