



SS Stainless Steel

Type

- DK** With triangular spindle
- VK7** With square spindle
- VK8** With square spindle
- SCH** With slot
- VDE** With double bit

Metric table



Dimensions in: millimeters - inches

Latch distance A													
6	10	14	18	20	22	24	26	28	30	34	38	40	50
0.24	0.39	0.55	0.71	0.79	0.87	0.94	1.02	1.10	1.18	1.34	1.50	1.57	1.97

Specification



- Cam latch housing
Stainless steel AISI 303 **NI**
- Latch arm
Stainless steel AISI 304
- Protection class IP 65
- IP Protection Classes → page 2130
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Accessory

- Socket keys GN 119.2 → page 1310
- Protective caps GN 120
→ www.jwwinco.com
- Opening handles GN 120.1
→ www.jwwinco.com
- Protective guide plates GN 120.2
→ www.jwwinco.com

Information

GN 115 stainless steel cam latches close via a turning operation limited to 90° (quarter of a turn), which moves the latch arm behind the door frame. The beveled edges of the latch arm create a smooth latching of the door.

The 14 different off-set latch arm options allow for "Latch distance A" to be set between 6 mm and 50 mm.

The operating bolt is assembled with an O-ring to seal the cam latch housing.

Product comes supplied with a loosely enclosed latch arm.

The socket key latches the latch arm and provides security from accidentally opening but does not lock the arm in place.

A socket key is not included.

see also...

- Construction and Assembly Instructions → page 1261
- List of Cam Latch / Cam Lock Types → page 1256
- Cam Locks GN 115 (Stainless Steel) → page 1268
- Cam Latches GN 115 (Zinc Die-Cast, with Operating Elements) → page 1260

How to order

GN 115-DK-18-NI

1	Type
2	Latch distance A
3	Material

