Double Arm Clamp Nuts

Cast Iron / Stainless Steel Precision Casting, Tapped Type

JW WINCO® A Ganter Company



Metric

SS Stainless Steel

Metric table

Dimensions in: millimeters / inches

1 d_1	2 d_2	a	b	h_1	h_2 ≈	Length l ≈
16 0.63	M 8	7 0.28	12 0.47	12 0.47	36 1.42	56 2.20
20 0.79	M 10	9 0.35	14 0.55	14 0.55	44.5 1.75	70 2.76
25 0.98	M 12	11 0.43	18 0.71	18 0.71	55 2.17	87 3.43
32 1.26	M 16	15 0.59	22 0.87	22 0.87	68.5 2.70	109 4.29
40 1.57	M 20	18 0.71	28 1.10	28 1.10	87 3.43	140 5.51

Specification

3

Cast iron —
- Fettled
- Contact faces machined

Stainless steel precision casting AISI CF-8 **NI**
- Fettled
- Contact faces machined

RoHS

On request

- Double arm clamp nuts GN 206.1, powder coated
- Special inch and metric bores or threads

Double arm clamp nuts GN 206.1 are solid components. They are a good choice for certain corrosion free environment applications.

see also...	Page
GN 99.7 Double Arm Clamp Nuts (Steel)	QVX
GN 99.8 Double Arm Clamp Nuts (Stainless Steel)	QVX

Technical Information

Stainless Steel Characteristics	QVX

How to order (Steel)		
GN 206.1-32-M16 (1 2)	1	Diameter d_1
	2	Thread d_2

How to order (Stainless steel)		
GN 206.1-20-M10-NI (1 2 3)	1	Diameter d_1
	2	Thread d_2
	3	Material

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov