



Inch table

Dimensions in: inches - millimeters

1			2		3					d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
l ₁	d ₁ Thread		l ₂												
4.72 120	3/8 x 16	1/2 x 13	.79 20	.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	.63 16	1.26 32	1.16 29.5	.08 2	1.63 41.5	.10 2.5
5.71 145	5/8 x 11	-	1.26 32	1.57 40	1.97 50	2.48 63	3.15 80	-	-	.91 23	1.57 40	1.65 42	.16 4	2.20 56	.16 4

Metric table

Dimensions in: millimeters - inches

1			2		3					d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
l ₁	d ₁ Thread		l ₂												
120 4.72	M 10	M 12	20 .79	25 .98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 .63	32 1.26	29.5 1.16	2 .08	41.5 1.63	2.5 .10
145 5.71	M 12	M 16	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	23 .91	40 1.57	42 1.65	4 .16	56 2.20	4 .16

Specification

- Lever body
Zinc die-cast
- Powder coated
Black, RAL 9005, textured finish ● SW
Silver, RAL 9006, textured finish ● SR
- Hub cover
Plastic
- Black for SW
- Light gray for SR
- Countersunk screw
Stainless steel
- Chemically blackened finish for SW
- Plain finish for SR
- GN 126**
Threaded stud
Steel, blackened finish
- GN 126.1**
Threaded stud
Stainless steel
European Standard No. 1.4305 (AISI 303)
- RoHS compliant

Information

GN 126 and GN 126.1 flat adjustable tension levers are characterized by their low height and the timelessly elegant design.

They have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Adjustable Levers GN 300 (with Steel Tapped Insert)
- Adjustable Levers GN 300.1 (with Stainless Steel Tapped Insert)
- Adjustable Levers GN 300.5 (Stainless Steel, Matte Shot-Blasted Finish)
- Flat Adjustable Tension Levers GN 125 (with Steel Threaded Stud)
- Flat Adjustable Tension Levers GN 125.5 (Stainless Steel)

How to order (Inch, steel threaded stud)	1 Lever length l ₁
	2 Thread d ₁
	3 Thread length l ₂
	4 Color
1 2 3 4 GN 126-120-3/8X16-20-SW	

How to order (Metric, stainless steel threaded stud)	1 Lever length l ₁
	2 Thread d ₁
	3 Thread length l ₂
	4 Color
1 2 3 4 GN 126.1-120-M10-40-SR	