



SS Stainless Steel

- 2 Type**
- A Without seals
 - B With seals

- 3 Identification no.**
- 4 With 2 stainless steel cap nuts DIN 917

Metric table

Dimensions in: millimeters - inches

d ₁ - d ₂		b	d ₃	d ₄	k	l ₁	m	z	Accessory	
One-Axis System GN 132.15 with sleeve bearing	Two-Axis System GN 132.25 with sleeve bearing			Mounting screws on the drive key	Clamping length			Screw locations for screw size	Recommended lever GN 911.3 for z l ₂	
G30 - B30	G30 - B30	22 0.87	37 1.46	M 4	40 1.57	104 4.09	33 1.30	M 8	63 2.48	78 3.07
G50 - B50	G50 - B50	30 1.18	60 2.36	M 6	65 2.56	150 5.91	53 2.09	M 10	78 3.07	92 3.62

Specification

- Body
Stainless steel AISI CF-8
Matte shot-blasted finish
- Sleeve bearing
Plastic (PTFE)
- Carriage bolt DIN 603
Stainless steel A2
- Cap nuts DIN 917 / washers
Stainless steel A2
- Seals
 - Sealing disks
Plastic (Polyacetal POM)
 - Spacer ring
Silicon, 40 ... 60 shore A
- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Accessory

- Adjustable levers GN 911.3

Information

Two-way linear actuator connectors GN 132.15 / GN 132.25 are based on two-way connector clamps. The additionally provided mounting holes are used to connect to the drive key of a linear actuator. Bores with the designation "G" are equipped with sleeve bearings.

With the screw locations z, the play of the guide bore d₁ / (d₂) can be adjusted or the linear actuator connectors can be clamped after adjustment. Type B is equipped with seals at the screw locations.

For quick clamping without tools, the cap nuts can be replaced by the adjustable levers GN 911.3 listed in the table as accessories.

see also...

- Construction Tubes GN 990 → page QVX
- Linear Actuators GN 291 → page QVX

How to order (For one-axis system)	1 Diameter d ₁ - d ₂
GN 132.15-G30-B30-A-4	2 Type
	3 Identification no.

How to order (For two-axis system)	1 Diameter d ₁ - d ₂
GN 132.25-G50-G50-B-4	2 Type
	3 Identification no.