



SS Stainless Steel

3 Type
E Angled lever

Inch table

Dimensions in: inches - millimeters

1 d_1	2 d_2 Thread		d_3	d_4	d_5	h_1	h_3	$h_4 \approx$	h_5 Stroke	$l_2 \approx$	$l_3 \approx$	t min.
.83 21	1/4 x 20	5/16 x 18	.53 13.5	.31 8	.79 20	1.32 33.5	.04 1	2.32 59	.16 4	2.95 75	2.76 70	.43 11
.94 24	5/16 x 18	3/8 x 16	.63 16	.39 10	.98 25	1.57 40	.10 2.5	2.95 75	.18 4.5	3.98 101	3.78 96	.55 14
1.10 28	3/8 x 16	1/2 x 13	.75 19	.47 12	1.18 30	1.91 48.5	.18 4.5	3.50 89	.18 4.5	4.57 116	4.33 110	.67 17

Metric table

Dimensions in: millimeters - inches

1 d_1	2 d_2 Thread		d_3	d_4	d_5	h_1	h_3	$h_4 \approx$	h_5 Stroke	$l_2 \approx$	$l_3 \approx$	t min.
21 .83	M 6	M 8	13.5 .53	8 .31	20 .79	33.5 1.32	1 .04	59 2.32	4 .16	75 2.95	70 2.76	11 .43
24 .94	M 8	M 10	16 .63	10 .39	25 .98	40 1.57	2.5 .10	75 2.95	4.5 .18	101 3.98	96 3.78	14 .55
28 1.10	M 10	M 12	19 .75	12 .47	30 1.18	48.5 1.91	4.5 .18	89 3.50	4.5 .18	116 4.57	110 4.33	17 .67

Specification

- Body / lever / insert
Stainless steel
European Standard No. 1.4305 (AISI 303),
matte shot-blasted finish
- Ball knob DIN 319
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Spring
Stainless steel
European Standard No. 1.4310 (AISI 301)
- RoHS compliant

On request

- Straight lever
- Special threads and stud lengths

Information

GN 212.5 stainless steel heavy duty adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upward disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Heavy Duty Adjustable Levers GN 212.3 (Steel, Blackened Finish)

How to order (Inch)	1 Diameter d_1
GN 212.5-21-1/4X20-E	2 Thread d_2
	3 Type

How to order (Metric)	1 Diameter d_1
GN 212.5-24-M10-E	2 Thread d_2
	3 Type