



- 2 Identification no.**
- 2 With 2 stainless steel socket cap screws DIN 912

Metric table

Dimensions in: millimeters - inches

d₁ Bore	s Square	d₂	k Clamping length	l₁	l₂	m	t	x₁	x₂	y₁	y₂	z Screw locations for screw size	Accessory Recommended lever GN 911 for z l₃	
B 20	V 20	6.5 0.26	50 1.97	53 2.09	68 2.68	30 1.18	7 0.28	50 1.97	35 1.38	75 2.95	60 2.36	M8-40	63 2.48	78 3.07
B 25	V 25	6.5 0.26	50 1.97	53 2.09	68 2.68	30 1.18	7 0.28	50 1.97	35 1.38	75 2.95	60 2.36	M8-40	63 2.48	78 3.07
B 30	V 30	6.5 0.26	50 1.97	53 2.09	68 2.68	30 1.18	7 0.28	50 1.97	35 1.38	75 2.95	60 2.36	M8-40	63 2.48	78 3.07
B 40	V 40	11 0.43	76 2.99	81.5 3.21	98 3.86	46.5 1.83	14 0.55	76 2.99	50 1.97	115 4.53	90 3.54	M10-65	78 3.07	92 3.62
B 42	-	11 0.43	76 2.99	81.5 3.21	98 3.86	46.5 1.83	14 0.55	76 2.99	50 1.97	115 4.53	90 3.54	M10-65	78 3.07	92 3.62
B 45	V 45	11 0.43	76 2.99	81.5 3.21	98 3.86	46.5 1.83	14 0.55	76 2.99	50 1.97	115 4.53	90 3.54	M10-65	78 3.07	92 3.62
B 48	-	11 0.43	76 2.99	81.5 3.21	98 3.86	46.5 1.83	14 0.55	76 2.99	50 1.97	115 4.53	90 3.54	M10-65	78 3.07	92 3.62
B 50	V 50	11 0.43	76 2.99	81.5 3.21	98 3.86	46.5 1.83	14 0.55	76 2.99	50 1.97	115 4.53	90 3.54	M10-65	78 3.07	92 3.62
B 60	V 60	11 0.43	90 3.54	98 3.86	108.5 4.27	56 2.20	14 0.55	90 3.54	64 2.52	140 5.51	113 4.45	M10-80	-	-

Specification

- Body
Aluminum
 - Powder coated
Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted finish **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Accessory

- Construction Tubes GN 990 → page 1836
- Adjustable levers GN 911 → page 1810

Information

The clamping bore of GN 147 flanged connector clamps is not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

see also...

- *Flanged Linear Actuator Connectors GN 147.1* → www.jwwinco.com

How to order GN 147-B25-2-SW	1 Bore d ₁ (Square s)
	2 Identification no.
	3 Finish