



- 2** Identification no.  
2 With 2 stainless steel socket cap screws DIN 912

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub> Bore	<b>1</b> s Square	d <sub>2</sub>	k Clamping length	l <sub>1</sub>	l <sub>2</sub>	m	t	x <sub>1</sub>	x <sub>2</sub>	y <sub>1</sub>	y <sub>2</sub>	y <sub>3</sub>	z Screw locations for screw size	<b>Accessory</b> Recommended lever GN 911 for z l <sub>3</sub>	
B 20	V 20	6.5 0.26	50 1.97	53 2.09	68 2.68	30 1.18	7 0.28	55 2.17	40 1.57	97.5 3.84	60 2.36	82.5 3.25	M8-35	63 2.48	78 3.07
B 25	V 25	6.5 0.26	50 1.97	53 2.09	68 2.68	30 1.18	7 0.28	55 2.17	40 1.57	97.5 3.84	60 2.36	82.5 3.25	M8-35	63 2.48	78 3.07
B 30	V 30	6.5 0.26	50 1.97	53 2.09	68 2.68	30 1.18	7 0.28	55 2.17	40 1.57	97.5 3.84	60 2.36	82.5 3.25	M8-35	63 2.48	78 3.07

**Specification**

- Body  
Aluminum  
- Powder coated  
Black, RAL 9005, textured finish ● **SW**  
- Plain, matte shot-blasted finish ○ **BL**
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

**Accessory**

- Adjustable levers GN 911 → page 1810

**On request**

- Linear actuator connectors GN 147.4

**Information**

The clamping bore of GN 147.3 flanged connector clamps is not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

see also...

- [Product Family Standard Parts for Profile Systems](#) → page 18
- [Construction Tubes GN 990](#) → page 1836

<b>How to order</b>	<b>1</b> Bore d <sub>1</sub> (Square s)
	<b>2</b> Identification no.
	<b>3</b> Finish

**GN 147.3-B25-2-SW**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

