



ELESA original design CFA-ERS

- 3 Type**
- C** 2x2 bores for countersunk screws

Metric table

Dimensions in: millimeters - inches

1		2		d ₁	d ₂	h ₁	h ₂	h ₃	h ₄	h ₅	l ₃	l ₄	m ₁ ±0.25	m ₂ ±0.25
l ₁ Nominal dimension	Actual dimension	l ₂ Nominal dimension	Actual dimension											
48	48	49	49.5	5.5	4	19	11	13	36	26	44	17	31	30
1.89	1.89	1.93	1.95	0.22	0.16	0.75	0.43	0.51	1.42	1.02	1.73	0.67	1.22	1.18
64	64	65	65	6.5	5	23	13.5	15	36	30	44	24	40	40
2.52	2.52	2.56	2.56	0.26	0.20	0.91	0.53	0.59	1.42	1.18	1.73	0.94	1.57	1.57
98	97.5	98	96.5	10.5	8	35	20.5	23	48	46	63	35	62.5	59.5
3.86	3.84	3.86	3.80	0.41	0.31	1.38	0.81	0.91	1.89	1.81	2.48	1.38	2.46	2.34

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish
- Temperature resistant up to 176 °F (80 °C)
- Pin
Steel, blackened finish
- Safety adjustable lever EN 604.2
Plastic
Technopolymer (Polyamide PA)
Black, matte finish
- RoHS compliant

Information

By utilizing EN 151.2 lockable hinges, doors, flaps, etc. can be locked in any position. When not engaged, the clamping lever is not connected to the hinge pin and is in a “free-wheeling” position. When the operator pushes down on the lever button, it engages itself in two notches and the hinge can be tightened or loosened. This prevents the hinge from being accidentally moved. It also ensures that the lever will never interfere with the movement of the hinge.

see also...

- List of Hinge Types
- Hinges EN 151 (Not Lockable)

How to order	1	Width l ₁
	2	Length l ₂
	3	Type
EN 151.2-64-65-C		

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10