



- 3 Type**
- A Exterior hinge wings
 - I Interior hinge wings
- 4 Identification**
- C With countersunk holes

Metric table

Dimensions in: millimeters - inches

1		2		d ₁	d ₂	l ₃	l ₄	l ₅	3		m ₂	m ₃	m ₄	s
l ₁	Type I	l ₂	Type I						Type A	Type I				
72	86	82	86	6.6	14	40	36	43	40.8	55	42	-	-	3.5
2.83	3.39	3.23	3.39	0.26	0.55	1.57	1.42	1.69	1.61	2.17	1.65	-	-	0.14
72	86	162	86	6.6	14	80	36	43	40.8	55	-	50	32	3.5
2.83	3.39	6.38	3.39	0.26	0.55	3.15	1.42	1.69	1.61	2.17	-	1.97	1.26	0.14

Specification

- Body
Aluminum
Anodized finish, natural color **EL**
- Bearing bushing / cover cap
Plastic
Technopolymer (Polyamide PA)
Gray, RAL 7035
- Tapered dowel pin ISO 8741
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

GN 2294 double winged hinges are made of drawn profiled aluminum and can be used on doors and covers.

External hinge wing, type A hinges, allow mounting with a very small door gap. Type I hinges are mounted between the door gap. This results in the mounting screws being hidden when the door is closed, which reduces the chance of vandalism.

The hinges are delivered loose and must be mounted according to the accompanying instructions. Any hinge combination may be created thanks to the modular design and available accessories.

see also...

- Product Range Profile Systems
- List of Hinge Types

On request

- Other lengths and hole spacings
- Other finishes

How to order	
1	Width l ₁
2	Length l ₂
3	Type
4	Identification
5	Finish

1 2 3 4 5
GN 2294-72-82-A-C-EL