


Metric



Metric table

¹ d_1	² d_2	d_3	l_1	l_2
12 0.47	M 4	9 0.35	40 1.57	8 0.31
15 0.59	M 5	11 0.43	50 1.97	7 0.28
18 0.71	M 6	13 0.51	64 2.52	8 0.31
21 0.83	M 6	15 0.59	72 2.83	10 0.39
21 0.83	M 8	15 0.59	72 2.83	10 0.39
25 0.98	M 8	17 0.67	90 3.54	10 0.39
26 1.02	M 10	20 0.79	100 3.94	12 0.47
33 1.30	M 12	25 0.98	124 4.88	14 0.55

Dimensions in: millimeters / inches

Specification

Handle

Plastic, Phenolic (PF)

- Operating temperature up to 230 °F (110 °C)
- Black, shiny finish

Threaded stud

Steel, zinc plated, blue passivated finish

RoHS

Fixed tapered handles GN 203 are used in applications where a positive non-revolving grip is required.

They are not suitable for applications where the handle is exposed to heavy loads. For applications with increased loads, see fixed cylindrical handles EN 539.

see also...

EN 539 Fixed Cylindrical Handles

Page

QVX

Technical Information

Plastic Characteristics

QVX

How to order

GN 203-15-M5

1 Handle diameter d_1 2 Thread d_2