


Inch | Metric



Inch table

1				2							Dimensions in: inches / millimeters	
l_1	d_1			d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.		
1.77 45	10 x 32	10 x 24	1/4 x 20	0.39 10	0.51 13	0.96 24.5	0.16 4	1.34 34	0.14 3.5	0.35 9		
2.48 63	1/4 x 20	5/16 x 18	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.77 45	0.16 4	0.43 11		
3.07 78	5/16 x 18	3/8 x 16	-	0.63 16	0.83 21	1.42 36	0.31 8	2.13 54	0.16 4	0.55 14		
3.62 92	3/8 x 16	1/2 x 13	-	0.75 19	0.94 24	1.69 43	0.43 11	2.52 64	0.16 4	0.67 17		
4.25 108	1/2 x 13	5/8 x 11	-	0.91 23	1.18 30	1.99 50.5	0.47 12	2.95 75	0.20 5	0.87 22		

Metric table

1				2							Dimensions in: millimeters / inches	
l_1	d_1			d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.		
22 0.87	M 3	M 4	M 5	8 0.31	10.5 0.41	18.5 0.73	2 0.08	23 0.91	3 0.12	5 0.20		
30 1.18	M 4	M 5	M 6	10 0.39	13 0.51	24.5 0.96	4 0.16	31 1.22	3.5 0.14	8 0.31		
45 1.77	M 4	M 5	M 6	10 0.39	13 0.51	24.5 0.96	4 0.16	34 1.34	3.5 0.14	8 0.31		
63 2.48	M 6	M 8	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	45 1.77	4 0.16	11 0.43		
78 3.07	M 8	M 10	-	16 0.63	21 0.83	36 1.42	8 0.31	54 2.13	4 0.16	14 0.55		
92 3.62	M 10	M 12	-	19 0.75	24 0.94	43 1.69	11 0.43	64 2.52	4 0.16	17 0.67		
108 4.25	M 12	M 16	-	23 0.91	30 1.18	50.5 1.99	12 0.47	75 2.95	5 0.20	22 0.87		

Specification

Lever body

Zinc die-cast

Powder coated

- Black, RAL 9005, textured finish
- Orange, RAL 2004, textured finish
- Red, RAL 3000, textured finish
- Silver, RAL 9006, textured finish

Chrome plated

Uncoated, tumbled finish

- SW
- OS
- RS
- SR
- CR
- RH

Tapped insert / Retaining screw

Steel, zinc plated, blue passivated finish

RoHS

Adjustable levers GN 300.2 have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The tapped insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

GN 300 Adjustable Levers (Steel Insert, Blackened Finish)

GN 300.1 Adjustable Levers (Stainless Steel Insert)

Page

QVX

QVX

How to order (Inch)

GN 300.2-63-1/4X20-SW

- Lever length l_1
- Thread d_1
- Color (Finish)

How to order (Metric)

GN 300.2-78-M10-OS

- Lever length l_1
- Thread d_1
- Color (Finish)