



- 3** Type
E Angled lever
D Straight lever

Inch table

1 **2**

d ₁	d ₂ Thread		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈		h ₅ Stroke	l ₂ ≈		l ₃ ≈	t min.
	Type E	Type D							Type E	Type D					
.83 21	1/4 x 20	5/16 x 18	.53 13.5	.31 8	.79 20	1.32 33.5	1.22 31	.04 1	2.32 59	1.42 36	.16 4	2.95 75	3.17 80.5	2.76 70	.43 11
.94 24	5/16 x 18	3/8 x 16	.63 16	.39 10	.98 25	1.57 40	1.46 37	.10 2.5	2.95 75	1.71 43.5	.18 4.5	3.98 101	4.25 108	3.78 96	.55 14
1.10 28	3/8 x 16	1/2 x 13	.75 19	.47 12	1.18 30	1.91 48.5	1.75 44.5	.18 4.5	3.50 89	2.07 52.5	.18 4.5	4.57 116	4.88 124	4.33 110	.67 17
1.30 33	1/2 x 13	5/8 x 11	.91 23	.47 12	1.26 32	2.17 55	2.03 51.5	.24 6	3.96 100.5	2.36 60	.22 5.5	5.18 131.5	5.53 140.5	4.88 124	.87 22
1.57 40	3/4 x 10	-	1.10 28	.55 14	1.38 35	2.68 68	2.52 64	.24 6	4.65 118	2.81 71.5	.22 5.5	5.83 148	6.22 158	5.43 138	1.42 36

Dimensions in: inches - millimeters

Metric table

1 **2**

d ₁	d ₂ Thread		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈		h ₅ Stroke	l ₂ ≈		l ₃ ≈	t min.
	Type E	Type D							Type E	Type D					
21 .83	M 6	M 8	13.5 .53	8 .31	20 .79	33.5 1.32	31 1.22	1 .04	59 2.32	36 1.42	4 .16	75 2.95	80.5 3.17	70 2.76	11 .43
24 .94	M 8	M 10	16 .63	10 .39	25 .98	40 1.57	37 1.46	2.5 .10	75 2.95	43.5 1.71	4.5 .18	101 3.98	108 4.25	96 3.78	14 .55
28 1.10	M 10	M 12	19 .75	12 .47	30 1.18	48.5 1.91	44.5 1.75	4.5 .18	89 3.50	52.5 2.07	4.5 .18	116 4.57	124 4.88	110 4.33	17 .67
33 1.30	M 12	M 14	23 .91	12 .47	32 1.26	55 2.17	51.5 2.03	6 .24	100.5 3.96	60 2.36	5.5 .22	131.5 5.18	140.5 5.53	124 4.88	22 .87
40 1.57	M 16	M 20	28 1.10	14 .55	35 1.38	68 2.68	64 2.52	6 .24	118 4.65	71.5 2.81	5.5 .22	148 5.83	158 6.22	138 5.43	36 1.42

Dimensions in: millimeters - inches

Specification

- Body / lever / insert
Steel, blackened finish
- Spring
Steel
- Ball knob DIN 319
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- RoHS compliant

Information

GN 212.3 heavy duty adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upward disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

How to order (Inch)	1 Diameter d ₁
GN 212.3-21-1/4X20-D	2 Thread d ₂
	3 Type

How to order (Metric)	1 Diameter d ₁
GN 212.3-28-M12-E	2 Thread d ₂
	3 Type