



3 Type
E Angled lever
D Straight lever

Inch table

1 **2**

Dimensions in: inches - millimeters

d ₁	d ₂ Thread		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈		h ₅ Stroke	l ₂ ≈		l ₃ ≈	t min.
	Type E	Type D							Type E	Type D					
.83 21	1/4 x 20	5/16 x 18	.53 13.5	.31 8	.79 20	1.32 33.5	1.22 31	.04 1	2.32 59	1.42 36	.16 4	2.95 75	3.17 80.5	2.76 70	.43 11
.94 24	5/16 x 18	3/8 x 16	.63 16	.39 10	.98 25	1.57 40	1.46 37	.10 2.5	2.95 75	1.71 43.5	.18 4.5	3.98 101	4.25 108	3.78 96	.55 14
1.10 28	3/8 x 16	1/2 x 13	.75 19	.47 12	1.18 30	1.91 48.5	1.75 44.5	.18 4.5	3.50 89	2.07 52.5	.18 4.5	4.57 116	4.88 124	4.33 110	.67 17
1.30 33	1/2 x 13	5/8 x 11	.91 23	.47 12	1.26 32	2.17 55	2.03 51.5	.24 6	3.96 100.5	2.36 60	.22 5.5	5.18 131.5	5.53 140.5	4.88 124	.87 22
1.57 40	3/4 x 10	-	1.10 28	.55 14	1.38 35	2.68 68	2.52 64	.24 6	4.65 118	2.81 71.5	.22 5.5	5.83 148	6.22 158	5.43 138	1.42 36

Metric table

1 **2**

Dimensions in: millimeters - inches

d ₁	d ₂ Thread		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈		h ₅ Stroke	l ₂ ≈		l ₃ ≈	t min.
	Type E	Type D							Type E	Type D					
21 .83	M 6	M 8	13.5 .53	8 .31	20 .79	33.5 1.32	31 1.22	1 .04	59 2.32	36 1.42	4 .16	75 2.95	80.5 3.17	70 2.76	11 .43
24 .94	M 8	M 10	16 .63	10 .39	25 .98	40 1.57	37 1.46	2.5 .10	75 2.95	43.5 1.71	4.5 .18	101 3.98	108 4.25	96 3.78	14 .55
28 1.10	M 10	M 12	19 .75	12 .47	30 1.18	48.5 1.91	44.5 1.75	4.5 .18	89 3.50	52.5 2.07	4.5 .18	116 4.57	124 4.88	110 4.33	17 .67
33 1.30	M 12	M 14	23 .91	12 .47	32 1.26	55 2.17	51.5 2.03	6 .24	100.5 3.96	60 2.36	5.5 .22	131.5 5.18	140.5 5.53	124 4.88	22 .87
40 1.57	M 16	M 20	28 1.10	14 .55	35 1.38	68 2.68	64 2.52	6 .24	118 4.65	71.5 2.81	5.5 .22	148 5.83	158 6.22	138 5.43	36 1.42

Specification

- Body / lever / insert
Steel, blackened finish
- Ball knob DIN 319
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Safety circlip
Plastic (Polyacetal POM)
- RoHS compliant

Information

GN 212.3 heavy duty adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

How to order (Inch)	1 Diameter d ₁
GN 212.3-21-1/4X20-D	2 Thread d ₂
	3 Type

How to order (Metric)	1 Diameter d ₁
GN 212.3-28-M12-E	2 Thread d ₂
	3 Type