



Specification

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Orange, RAL 2004, textured finish ● **OS**
 - Red, RAL 3000, textured finish ● **RS**
 - Silver, RAL 9006, textured finish ● **SR**
- Chrome plated finish ● **CR**
- Uncoated, tumbled finish ○ **RH**
- Insert / retaining screw
Steel, blackened finish
- *ISO Fundamental Tolerances* → page 2129
- [RoHS compliant](#)

On request

- Black, RAL 9011, silk shiny finish ● **SZ**
- Special colors, bores, and threads

Information

GN 300 adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- *Adjustable Levers GN 300.1 (with Stainless Steel Insert)* → page 406
- *Adjustable Levers GN 300.5 (Stainless Steel, Matte Shot-Blasted Finish)* → page 430
- *Straight Adjustable Levers GN 302* → page 452
- *Adjustable Levers GN 300.4 (with Secure Clamping Force)* → page 426
- *Adjustable Levers GN 303 (with Push Button)* → page 440

How to order (Inch)	1 Lever length l_1
1 2 3	2 Thread d_1 (Bore d_2)
GN 300-30-10X32-SW	3 Color (Finish)

How to order (Metric)	1 Lever length l_1
1 2 3	2 Bore d_2 (Thread d_1)
GN 300-92-B12-SR	3 Color (Finish)

Inch table

Dimensions in: inches - *millimeters*

I ₁	d ₁ Thread			d ₂ +0.001 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
	6 x 32	8 x 32	10 x 32	-	B 1/4							
0.87 22	6 x 32	8 x 32	10 x 32	-	B 1/4	0.31 8	0.41 10.5	0.73 18.5	0.08 2	0.91 23	0.12 3	0.20 5
1.18 30	10 x 32	10 x 24	1/4 x 20	B 1/4	B 1/4	0.39 10	0.51 13	0.96 24.5	0.16 4	1.22 31	0.14 3.5	0.35 9
1.77 45	10 x 32	10 x 24	1/4 x 20	B 1/4	B 1/4	0.39 10	0.51 13	0.96 24.5	0.16 4	1.34 34	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	B 5/16	B 5/16	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.77 45	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	-	B 3/8	B 3/8	0.63 16	0.83 21	1.42 36	0.31 8	2.13 54	0.16 4	0.55 14
3.62 92	3/8 x 16	1/2 x 13	-	B 1/2	B 1/2	0.75 19	0.94 24	1.69 43	0.43 11	2.52 64	0.16 4	0.67 17
4.25 108	1/2 x 13	5/8 x 11	-	B 1/2	B 1/2	0.91 23	1.18 30	1.99 50.5	0.47 12	2.95 75	0.20 5	0.87 22

Metric table

Dimensions in: millimeters - *inches*

I ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
	M 3	M 4	M 5	B 4	B 5							
22 0.87	M 3	M 4	M 5	B 4	B 5	8 0.31	10.5 0.41	18.5 0.73	2 0.08	23 0.91	3 0.12	5 0.20
30 1.18	M 3	-	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	31 1.22	3.5 0.14	7 0.28
30 1.18	M 4	M 5	M 6	B 5	B 6	10 0.39	13 0.51	24.5 0.96	4 0.16	31 1.22	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	B 5	B 6	10 0.39	13 0.51	24.5 0.96	4 0.16	34 1.34	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	B 8	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	45 1.77	4 0.16	11 0.43
78 3.07	M 8	M 10	M 12	B 8	B 10	16 0.63	21 0.83	36 1.42	8 0.31	54 2.13	4 0.16	14 0.55
92 3.62	M 10	M 12	-	B 12	-	19 0.75	24 0.94	43 1.69	11 0.43	64 2.52	4 0.16	17 0.67
108 4.25	M 12	M 14	M 16	B 12	B 16	23 0.91	30 1.18	50.5 1.99	12 0.47	75 2.95	5 0.20	22 0.87

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

