



SS Stainless Steel

3 Type
E Angled lever

Inch table

Dimensions in: inches - millimeters

1 d ₁	2 d ₂ Thread		d ₃	d ₄	d ₅	h ₁	h ₃	h ₄ ≈	h ₅ Stroke	l ₂ ≈	l ₃ ≈	t min.
.83 21	1/4 x 20	5/16 x 18	.53 13.5	.31 8	.79 20	1.32 33.5	.04 1	2.32 59	.16 4	2.95 75	2.76 70	.43 11
.94 24	5/16 x 18	3/8 x 16	.63 16	.39 10	.98 25	1.57 40	.10 2.5	2.95 75	.18 4.5	3.98 101	3.78 96	.55 14
1.10 28	3/8 x 16	1/2 x 13	.75 19	.47 12	1.18 30	1.91 48.5	.18 4.5	3.50 89	.18 4.5	4.57 116	4.33 110	.67 17

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread		d ₃	d ₄	d ₅	h ₁	h ₃	h ₄ ≈	h ₅ Stroke	l ₂ ≈	l ₃ ≈	t min.
21 .83	M 6	M 8	13.5 .53	8 .31	20 .79	33.5 1.32	1 .04	59 2.32	4 .16	75 2.95	70 2.76	11 .43
24 .94	M 8	M 10	16 .63	10 .39	25 .98	40 1.57	2.5 .10	75 2.95	4.5 .18	101 3.98	96 3.78	14 .55
28 1.10	M 10	M 12	19 .75	12 .47	30 1.18	48.5 1.91	4.5 .18	89 3.50	4.5 .18	116 4.57	110 4.33	17 .67

Specification

- Body / lever / insert
Stainless steel
European Standard No. 1.4305 (AISI 303),
matte shot-blasted finish
- Ball knob DIN 319
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- RoHS compliant

Information

GN 212.5 heavy duty adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Heavy Duty Adjustable Levers GN 212.3 (Steel, Blackened Finish)

On request

- Straight lever
- Special threads and stud lengths

How to order (Inch)	1 Diameter d ₁
GN 212.5-21-1/4X20-E	2 Thread d ₂
	3 Type

How to order (Metric)	1 Diameter d ₁
GN 212.5-24-M10-E	2 Thread d ₂
	3 Type