



**Metric table**

Dimensions in: millimeters - inches

1	2	3											
$l_1$	$d_1$ Thread	$l_2$		$d_2$	$d_3$	$d_4$	$h_1$	$h_2$	$h_3$	$h_4$ Stroke			
63 2.48	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	14 0.55	14.8 0.58	19 0.75	43.8 1.72	16.3 0.64	60.1 2.37	2.5 0.10
63 2.48	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	18 0.71	18.8 0.74	19 0.75	45.8 1.80	18.3 0.72	62.1 2.44	2.5 0.10
78 3.07	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	18 0.71	18.8 0.74	24 0.94	49.3 1.94	16.5 0.65	69.3 2.73	3 0.12
78 3.07	M 10	16 0.63	20 0.79	25 0.98	32 1.26	-	22 0.87	22.8 0.90	24 0.94	51.3 2.02	18.5 0.73	71.3 2.81	3 0.12

**Specification**

- Lever body  
Stainless steel precision casting  
AISI CF-8  
Polished finish (Ra < 0.8 μm) **PL**
- Threaded stud  
Stainless steel AISI 304
- Sealing ring / wiper **H**  
H-NBR  
- Blue  
- Temperature resistant from -13 °F to +302 °F (-25 °C to +150 °C)  
- Hardness 85 ±5 shore A  
- FDA compliant
- Stainless Steel Characteristics
- Elastomer Characteristics
- RoHS compliant

**Information**

GN 305 adjustable levers with solid stainless steel lever body are intended for use in hygienic design applications. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the impervious exterior surfaces prevent adherence of dirt and facilitates cleaning.

Adjustable levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position.

The tapped insert is moveably attached to the handle with serrations. When pulling up on the handle the serration frees itself and can be re-located into any required position. Engagement is achieved by releasing the lever.

see also...

- Product Family *Hygienic Design*
- Star Knobs GN 5435 *Hygienic Design*
- Three Lobe Knobs GN 5445 *Hygienic Design*

**Accessory**

- Sealing rings GN 7600

**How to order**

1	Lever length $l_1$
2	Thread $d_1$
3	Thread length $l_2$
4	Finish
5	Sealing ring material

**GN 305-78-M10-20-PL-H**