



Metric



**Metric table**

Dimensions in: millimeters / inches

<b>d<sub>0</sub></b> = Shaft collar Ø d <sub>1</sub>	<b>1</b>	<b>2</b>	<b>3</b>	<b>l<sub>1</sub></b>	<b>d<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>l<sub>2</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>3</sub></b>
16 0.63	-	22 0.87	M 3	7 0.28	5.7 0.22	10.5 0.41	8 0.31	24 0.94	22 0.87		
20 0.79	22 0.87	22 0.87	M 3	8 0.31	5.7 0.22	10.5 0.41	10 0.39	24 0.94	22 0.87		
26 1.02	-	22 0.87	M 4	9 0.35	7.2 0.28	10.5 0.41	10 0.39	26 1.02	24 0.94		
30 1.18	32 1.26	30 1.18	M 4	12 0.47	7.2 0.28	13 0.51	12 0.47	32 1.26	30 1.18		
36 1.42	-	30 1.18	M 5	13 0.51	8.7 0.34	13 0.51	12 0.47	33.5 1.32	31 1.22		
42 1.65	-	30 1.18	M 5	15 0.59	8.7 0.34	13 0.51	14 0.55	35 1.38	33 1.30		
48 1.89	-	45 1.77	M 5	16 0.63	8.7 0.34	13 0.51	16 0.63	36.5 1.44	34 1.34		
55 2.17	-	45 1.77	M 6	18 0.71	10 0.39	13 0.51	16 0.63	38.5 1.52	36 1.42		
60 2.36	-	45 1.77	M 6	19 0.75	10 0.39	13 0.51	16 0.63	39.5 1.56	37 1.46		
65 2.56	-	45 1.77	M 6	20 0.79	10 0.39	13 0.51	18 0.71	40.5 1.59	38 1.50		

**Specification**

**Handle**

Zinc die-cast, powder coated  
Black, RAL 9005, textured finish



**Threaded stud**

Stainless steel AISI 303

**Retaining screw**

Stainless steel AISI 304

RoHS

For shaft collars of the series GN 706... and GN 707..., the adjustable lever GN 311 replaces the socket cap screw DIN 912. The lever allows the shaft collars to be adjusted easily and quickly without tools.

The table of dimensions of these shaft collars shows the suitable adjustable lever for the respective shaft collar size d<sub>1</sub>.

Semi-split shaft collars GN 706.2 including adjustable lever are available under GN 706.4.

see also...

	Page
GN 706.2 Semi-Split Shaft Collars	QVX
GN 707.2 Split Shaft Collars	QVX
GN 706.4 Semi-Split Shaft Collars (with Adjustable Lever)	QVX

**Technical Information**

Stainless Steel Characteristics

QVX

**How to order**

**GN311-30-M5-15-SW**

- 1** Lever length l<sub>1</sub>
- 2** Thread d<sub>1</sub>
- 3** Height h<sub>2</sub>
- 4** Color

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

