



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Ø Insert	² d ₂ Thread	² d ₃ H7 Bore with keyway		² s ₁ Square		² s ₂ Hexagon	b	d ₄	d ₅	h	Length l	Max. torque in Nm
12 .47	M 8	-	-	-	V 8	-	22 .87	9 .35	20 .79	11 .43	118 4.65	40
17 .67	M 10	M 12	K 10	K 12	V 10	-	30 1.18	11 .43	26 1.02	14 .55	156 6.14	70
22 .87	M 14*	M 16	K 14	K 16	V 12	V 14	39.5 1.56	14 .55	33 1.30	17 .67	187 7.36	130
26 1.02	M 20	-	K 18	-	V 17	-	46 1.81	17 .67	33 1.30	22 .87	219 8.62	180

* Not available from stock, requires a minimum order quantity

Specification

- Housing
Steel, powder coated
Black, matte textured finish
- Wrench arm
Stainless steel
European Standard No. 1.4305 (AISI 303),
matte shot-blasted finish
- Insert
Steel, hardened
- Domed gear lever knob GN 719.1
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- RoHS compliant

Information

GN 316 ratchet wrenches are robust, easy to handle and have an appropriate and attractive design. Ratchet wrenches are normally used wherever the same ratchet insert is always required or where it makes sense to leave the ratchet wrench at the place of use. That can mean, attaching it to equipment or machinery as a „stationary“ tool. Various versions of ratchet inserts are available, and these can be exchanged as needed by loosening the retaining screw and removing the cover plate. The ratchet action is deactivated when the reversing lever is in the locked position (central position), allowing torque to be applied in both directions.

see also...

- Countersunk Washers GN 184 (for Axial Fixing)

On request

- Modified inserts
- Other handle lengths

<p>How to order</p> <p>¹ ²</p> <p>GN 316-26-V17</p>	1	Insert diameter d ₁
	2	Square bore s ₁ (Hexagon bore s ₂ , Thread d ₂ , Bore with keyway d ₃)