



d ₁	d ₂	Static load in kN				
		Versions of threaded stem				
		S / SK	T / TK and U / UK	V / VK	W	X
80	M 8	6	-	-	-	17
80	M 10	11	-	-	-	17
80	M 12	16	-	-	-	17
80	M 16	-	17	21	25	17
80	M 20	-	28	35	35	28
80	M 24	-	46	52	52	-
100	M 8	6	-	-	-	17
100	M 10	11	-	-	-	17
100	M 12	16	-	-	-	17
100	M 16	-	17	21	25	17
100	M 20	-	28	35	35	28
100	M 24	-	46	52	52	-
120	M 20	-	28	-	-	28
120	M 24	-	46	-	-	-
120	M 30	-	43	-	-	-

Information

At a spindle thread size M 10 and higher, the static load of the Stainless Steel-Leveling feet GN 21 / GN 23 is limited owing to the permissible contact pressure of the adjustment spindle acting on the base plate (at a spindle strength $\geq 500 \text{ N/mm}^2$). The values given in the table (valid for type D0 without rubber underlay) assume a clean pressure load perpendicular to the base plate. Bending and buckling stress which often occurs in practice results in a lower load-bearing capacity of the adjustment spindle and may have to be taken into account.

The details given on strength are non-binding guide values without any liability. In general, they do not constitute a warranty of quality.

The user must determine from case to case if a product is suitable for the intended purpose or use. Environmental factors may influence the stated values.

