



Metric table

Dimensions in: millimeters - inches

d₁	d₂ Thread	d₃	h	Length l ±0.25	t min.
18 .71	M 6	12 .47	42 1.65	100 3.94	12 .47
20 .79	M 8	14 .55	47 1.85	112 4.41	15 .59
22 .87	M 10	16 .63	53 2.09	125 4.92	18 .71
25 .98	M 12	18 .71	59 2.32	140 5.51	20 .79

Specification

- Cast iron (GS45)
 - Powder coated
 - Black, RAL 9005, textured finish
● **SW**
 - Blank, unfinished casting, deburred
 - **BL**
- Contact surface machined
- RoHS compliant

Information

GN 225 cabinet “U” handles are of simple and solid design. They are best chosen when handles need to be plated or painted.

The tapped holes and contact faces are square and parallel.

see also...

- Round Cabinet “U” Handles GN 425 (Steel)

On request

- Various metric size fasteners and kit packaging

<p style="color: red; font-weight: bold; margin: 0;">How to order</p> <div style="display: flex; justify-content: center; align-items: center; gap: 10px;"> 1 2 </div> <p style="font-weight: bold; margin: 5px 0 0 0;">GN 225-20-SW</p>	<p>1 Handle diameter d₁</p> <hr style="border: 0.5px solid black;"/> <p>2 Finish</p>
--	---