


Application example



SS Stainless Steel

2 Type

- A** Without thread coating
- PRB** With thread coating (Polyamide all-round coating)

Metric table

1

Dimensions in: millimeters - inches

d		h	A/F
GN 252	GN 252.5		
M 12 x 1.5	M 12 x 1.5	10 .39	6 .24
M 16 x 1.5	M 16 x 1.5	10 .39	8 .31
M 20 x 1.5	M 20 x 1.5	12 .47	10 .39
M 24 x 1.5	M 24 x 1.5	12 .47	14 .55
M 27 x 1.5	M 27 x 1.5	12 .47	14 .55
M 30 x 1.5	-	12 .47	17 .67
M 33 x 1.5	-	12 .47	17 .67

Specification

- **GN 252**
Steel
 - Tensile strength class 5.8
 - Blackened finish
- **GN 252.5**
Stainless steel
European Standard No. 1.4305 (AISI 303)
- **RoHS compliant**

Information

GN 252 and GN 252.5 threaded plugs can be used as a spring retention unit as shown above or, as a plug to keep debris from entering into a critical threaded area.

The PRB thread coating (Polyamide - applied around the complete circumference) acts as a thread lock, preventing the threaded plug from being inadvertently loosened and becoming detached.

see also...

- *More Information on Thread Lockings*
- *Threaded Plugs GN 749 (with Rubber Sealing)*
- *Threaded Plugs DIN 906 (with Tapered Thread)*
- *Threaded Plugs DIN 908*

How to order (Steel) GN 252-M24X1.5-A	1 Thread d
	2 Type

How to order (Stainless steel) GN 252.5-M16x1.5-PRB	1 Thread d
	2 Type