



- 4 Type**
- A** 2x2 bores for countersunk screws
- 5 Identification no.**
- 1** Fixed bearing (pin) right
- 2** Fixed bearing (pin) left

Metric table

Dimensions in: millimeters - inches

1	2	3									
l_1	l_2	$d_1 +0.5$	d_2	h_1	h_2	h_3	h_4	l_3	$m_1 \pm 0.25$	$m_2 \pm 0.25$	
40 1.57	40 1.57	4 0.16	4 0.16	9 0.35	5 0.20	5.5 0.22	11 0.43	14 0.55	25 0.98	25 0.98	
50 1.97	50 1.97	6 0.24	6 0.24	11.5 0.45	6 0.24	6.5 0.26	13 0.51	18 0.71	30 1.18	30 1.18	
60 2.36	60 2.36	6 0.24	6 0.24	15 0.59	8 0.31	8.5 0.33	17 0.67	26 1.02	36 1.42	36 1.42	
60 2.36	60 2.36	8 0.31	8 0.31	15 0.59	8 0.31	8.5 0.33	17 0.67	26 1.02	36 1.42	36 1.42	

Specification

- Body
Plastic
Technopolymer (Polyamide PA-HP)
- Glass fiber reinforced
- Temperature resistant up to
212 °F (100 °C)
- Black, matte finish



- Pin
Plastic
Technopolymer (Polyamide PA)
Glass fiber reinforced

• Load Rating Information → page 2095

• Plastic Characteristics → page 2135

• RoHS compliant

Information

EN 337.1 lift-off hinges are designed so the two sides of the hinge can be easily detached from one another.

see also...

- List of Hinge Types → page 1324
- Hinges EN 237.1 (Non Lift-Off) → page 1334
- Spacer Plates GN 2370 (Stainless Steel) → page 1380
- Spacer Plates with Tapped Holes GN 2372 (Stainless Steel) → page 1381
- Limit Stops GN 2374 → page 1336

How to order	
1	Width l_1
2	Length l_2
3	Bore diameter d_1
4	Type
5	Identification no.
6	Color

EN 337.1-60-60-8-A-1-SW