



Metric table

Dimensions in: millimeters - inches

| ¹ d ₁ | ² d ₂ Thread | d ₃ | d ₄ | h | k | t |
|-----------------------------|---------------------------------------|----------------|----------------|------------|------------|-------------|
| 36 1.42 | M 8 M 10 M 12 | 5.3 0.21 | 10 0.39 | 10 0.39 | 24 0.94 | 5.3 0.21 |

Specification

- Mounting plate
Steel
- Weldable
- Blackened finish
- RoHS compliant

Information

GN 349 threaded mounting plates are used in conjunction with leveling feet, particularly in instances where the application is made of thin walls.

| | |
|--|---------------------------|
| <p>How to order</p> <p>¹ ²</p> <p>GN 349-36-M10</p> | 1 Diameter d ₁ |
| | 2 Thread d ₂ |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10