



2 Type

- OZ** Without centering step (smooth)
- MZ** With centering step
- AV** With external serration
- IV** With internal serration

Metric table

1

Dimensions in: millimeters - inches

b Swivel width	d ₁	d ₂	Length l	m ₁	m ₂	t ₁	t ₂	s	x ₁	x ₂	y ₁	y ₂
40 1.57	8.5 0.33	6.5 0.26	52.5 2.07	32.5 1.28	30 1.18	20 0.79	7 0.28	13 0.51	60 2.36	42 1.65	60 2.36	42 1.65
65 2.56	10.2 0.40	11 0.43	84.5 3.33	52 2.05	52.5 2.07	32.5 1.28	14 0.55	17 0.67	105 4.13	74 2.91	105 4.13	74 2.91

Specification

3

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Plain, matte shot-blasted finish
- RoHS compliant

- **SW**
- **BL**

Information

GN 272 swivel clamp connector bases can be combined with GN 274, GN 276 or GN 278 swivel clamp connectors to swivel clamp connector joints.

see also...

- Swivel Clamp Connector Joints GN 282 (Combination of GN 272 with GN 276) → page QVX
- Sensor Brackets GN 272.4 → page QVX

How to order

GN 272-40-OZ-BL

- 1** Swivel width b
- 2** Type
- 3** Finish