




Specification

Lever body
Zinc die-cast

- Powder coated
 - Black, RAL 9005, textured finish
 - Orange, RAL 2004, textured finish
 - Red, RAL 3000, textured finish
 - Silver, RAL 9006, textured finish
- Chrome plated
- Uncoated, tumbled finish

- **SW**
- **OS**
- **RS**
- **SR**
- **CR**
- **RH**

Threaded stud / Retaining screw
Steel, zinc plated, blue passivated finish

RoHS

Adjustable levers GN 300.2 have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The tapped insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

	Page
GN 300 Adjustable Levers (Steel Threaded Stud, Blackened Finish)	QVX
GN 300.1 Adjustable Levers (Stainless Steel Threaded Stud)	QVX
GN 300.5 Adjustable Levers (Stainless Steel)	QVX
GN 303.2 Adjustable Levers (Steel Threaded Stud Zinc Die-Cast, with Push Button)	QVX

Technical Information

Strength Values of Screws

QVX

Inch table

Dimensions in: inches / millimeters																
1	2	3														
l₁	d₁	l₂									d₃	d₄	h₁	h₂	h₃	h₄ Stroke
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	1.34 34	0.14 3.5
1.77 45	10 x 24	0.63 16	0.79 20	1.26 32	-	-	-	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	1.34 34	0.14 3.5
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.51 13	0.96 24.5	0.16 4	1.34 34	0.14 3.5
2.48 63	1/4 x 20	0.63 16	0.79 20	0.98 25	-	-	-	-	-	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.77 45	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.77 45	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.83 21	1.42 36	0.31 8	2.13 54	0.16 4
3.07 78	1/2 x 13	1.26 32	1.57 40	-	-	-	-	-	-	-	0.63 16	0.83 21	1.42 36	0.31 8	2.13 54	0.16 4
3.62 92	3/8 x 16	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	0.94 24	1.69 43	0.43 11	2.52 64	0.16 4
3.62 92	1/2 x 13	0.98 25	1.26 32	1.38 35	1.57 40	1.77 45	1.97 50	2.48 63	-	-	0.75 19	0.94 24	1.69 43	0.43 11	2.52 64	0.16 4
4.25 108	1/2 x 13	1.57 40	2.17 55	2.48 63	-	-	-	-	-	-	0.91 23	1.18 30	1.99 50.5	0.47 12	2.95 75	0.20 5
4.25 108	5/8 x 11	1.57 40	2.17 55	2.48 63	3.15 80	-	-	-	-	-	0.91 23	1.18 30	1.99 50.5	0.47 12	2.95 75	0.20 5

Metric table

Dimensions in: millimeters / inches																
1	2	3														
l₁	d₁	l₂									d₃	d₄	h₁	h₂	h₃	h₄ Stroke
22 0.87	M 3	-	6 0.24	8 0.31	10 0.39	12 0.47	16 0.63	-	-	-	8 0.31	10.5 0.41	18.5 0.73	2 0.08	23 0.91	3 0.12
22 0.87	M 4	M 5	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	8 0.31	10.5 0.41	18.5 0.73	2 0.08	23 0.91	3 0.12
30 1.18	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	31 1.22	3.5 0.14
30 1.18	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	13 0.51	24.5 0.96	4 0.16	31 1.22	3.5 0.14
45 1.77	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	34 1.34	3.5 0.14
45 1.77	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	13 0.51	24.5 0.96	4 0.16	34 1.34	3.5 0.14
63 2.48	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	45 1.77	4 0.16
78 3.07	M 8	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	16 0.63	21 0.83	36 1.42	8 0.31	54 2.13	4 0.16
92 3.62	M 10	M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	19 0.75	24 0.94	43 1.69	11 0.43	64 2.52	4 0.16
108 4.25	M 16	-	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	-	23 0.91	30 1.18	50.5 1.99	12 0.47	75 2.95	5 0.20