



Metric table

Dimensions in: millimeters - inches

d ₁	b	d ₂	h ₁	h ₂	h ₃	A/F	Max. permissible torque in Nm
12 <i>0.47</i>	2 <i>0.08</i>	11 <i>0.43</i>	35 <i>1.38</i>	7 <i>0.28</i>	6 <i>0.24</i>	8	20
18 <i>0.71</i>	2 <i>0.08</i>	17 <i>0.67</i>	39 <i>1.54</i>	8 <i>0.31</i>	9 <i>0.35</i>	11	50
24 <i>0.94</i>	4 <i>0.16</i>	22.5 <i>0.89</i>	43 <i>1.69</i>	9 <i>0.35</i>	12 <i>0.47</i>	13	75
30 <i>1.18</i>	4 <i>0.16</i>	28.5 <i>1.12</i>	48 <i>1.89</i>	11 <i>0.43</i>	15 <i>0.59</i>	17	100
36 <i>1.42</i>	4 <i>0.16</i>	34.5 <i>1.36</i>	53 <i>2.09</i>	13 <i>0.51</i>	18 <i>0.71</i>	22	150

Specification

- Steel
 - Surface hardened
 - Blackened finish
- RoHS compliant

Information

GN 355.1 assembly tools serve to adjust GN 355 / GN 355.2 leveling elements. The tool is used along with a T-handle or L-shaped hexagon key. To ease leveling, the top end of the assembly tool has an external hexagon head which is used for turning the leveling screw with a box-end wrench, ideally with a ratcheting function.

For adjustment, first use the assembly tool to turn the leveling screw of the leveling element into the desired position and at the same time tighten the screw to secure the leveling element. To ensure that the position does not change, the assembly tool may be used to counterhold the leveling element.

How to order	1 Diameter d ₁
GN 355.1-36	

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10