



Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Thread	d ₃	d ₄	h ₁	h ₃	h ₄ Stroke	t min.
63 2.48	M 6	24 0.94	17.5 0.69	34.5 1.36	48.5 1.91	4 0.16	12.5 0.49
78 3.07	M 8	25 0.98	21 0.83	39.5 1.56	58.5 2.30	4 0.16	14 0.55
92 3.62	M 10	30 1.18	24 0.94	46.5 1.83	68.5 2.70	4 0.16	18 0.71
108 4.25	M 12	35 1.38	30 1.18	56.5 2.22	82 3.23	5 0.20	26.5 1.04

Specification

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Orange, RAL 2004, textured finish ● **OS**
 - Red, RAL 3000, textured finish ● **RS**
 - Silver, RAL 9006, textured finish ● **SR**
- Chrome plated finish ● **CR**
- Tapped insert
Steel, nitrided, blackened finish
- Axial bearing / retaining screw
Steel, blackened finish
- RoHS compliant

On request

- Black, RAL 9011, silk shiny finish ● **SZ**

Information

An extension of the GN 300 version, the GN 300.4 adjustable levers function the same as normal adjustable levers, but are produced with a clamping area which is linked via an axial bearing to the insert and screw of the adjustable lever.

This design creates a clamping force that is doubled through vastly reduced friction. There is no movement on the contact area between the lever and component, greatly reducing any marring of the surface of the clamping area. The increased clamping force also results in a reduced creep factor.

How to order GN 300.4-78-M8-SW	¹	Lever length l ₁
	²	Thread d ₁
	³	Color (Finish)