



**2** Bore code  
B Without keyway

### Specification

- Aluminum
  - Contact face of hub machined
  - Rim turned and highly polished on all sides
- Rim concentric and square to bore < 0.4 mm
- Wheel body
  - Unmachined, matte shot-blasted finish
- RoHS compliant

### Information

DIN 3670 solid disk handwheels have recessed grips at their back. As a rule they are supplied without handle, but the mounting of a handle is possible.

see also...

- Countersunk Washers GN 184 (for Axial Fixing)

### On request

- Other modifications such as special inch and metric bores, keyways, set screw holes, etc.

How to order (Inch)	1 Handwheel diameter $d_1$
<b>DIN 3670-80-B1/2</b>	2 Bore code
	3 Bore diameter $d_2$
How to order (Metric)	1 Handwheel diameter $d_1$
<b>DIN 3670-200-B18</b>	2 Bore code
	3 Bore diameter $d_2$

### Inch table

Dimensions in: inches - *millimeters*

<b>d<sub>1</sub></b>	<b>d<sub>2</sub> +0.001 Bore</b>	<b>d<sub>3</sub></b>	<b>b</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub> ≈</b>
3.15 80	1/2	1.02 26	.55 14	.63 16	1.14 29
3.94 100	1/2	1.10 28	.59 15	.67 17	1.30 33
4.92 125	1/2	1.22 31	.63 16	.71 18	1.42 36
6.30 160	5/8	1.42 36	.71 18	.79 20	1.57 40
7.87 200	3/4	1.65 42	.87 22	.94 24	1.77 45
9.84 250	7/8	1.89 48	1.02 26	1.10 28	1.97 50

### Metric table

Dimensions in: millimeters - *inches*

<b>d<sub>1</sub></b>	<b>d<sub>2</sub> H7 Bore</b>			<b>d<sub>3</sub></b>	<b>b</b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub> ≈</b>
80 3.15	10	12	-	26 1.02	14 .55	16 .63	29 1.14
100 3.94	10	12	-	28 1.10	15 .59	17 .67	33 1.30
125 4.92	12	14	-	31 1.22	16 .63	18 .71	36 1.42
160 6.30	14	16	-	36 1.42	18 .71	20 .79	40 1.57
200 7.87	18	20	22	42 1.65	22 .87	24 .94	45 1.77
250 9.84	22	24	26	48 1.89	26 1.02	28 1.10	50 1.97
315 12.40	26	28	30	56 2.20	28 1.10	33 1.30	56 2.20
400 15.75	30	32	-	65 2.56	32 1.26	38 1.50	63 2.48

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

