



Metric table

Dimensions in: millimeters - inches

1	2	3						4	5	6	7	8
l_1	d_1 Thread	l_2					d_3	d_4	h_1	h_3	h_4 Stroke	
63 2.48	M 6	20 .79	27 1.06	-	-	-	24 .94	17.5 .69	34.5 1.36	48.5 1.91	4 .16	
78 3.07	M 8	21 .83	36 1.42	-	-	-	25 .98	21 .83	39.5 1.56	58.5 2.30	4 .16	
92 3.62	M 10	29 1.14	47 1.85	-	-	-	30 1.18	24 .94	46.5 1.83	68.5 2.70	4 .16	
108 4.25	M 12	34 1.34	50 1.97	57 2.24	65 2.56	85 3.35	35 1.38	30 1.18	56.5 2.22	82 3.23	5 .20	

Specification



- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Orange, RAL 2004, textured finish **● OS**
 - Red, RAL 3000, textured finish **● RS**
 - Silver, RAL 9006, textured finish **● SR**
- Chrome-plated finish **● CR**
- Threaded stud
Steel
 - Nitrided, blackened finish
 - Tensile strength class 5.8
- Thrust bearing / retaining screw
Steel, blackened finish
- Spring
Stainless steel
European Standard No. 1.4310 (AISI 301)
- RoHS compliant

Information

GN 300.4 adjustable levers are produced with a clamping area which is linked via a thrust ball bearing to the insert and screw of the adjustable lever.

This design results in doubled clamping force through vastly reduced friction. There is no movement on the contact area between the lever and component, greatly reducing any marking on the clamping area. The increased clamping force results in a reduced creep factor.

On request

- Black, RAL 9011, silk shiny finish **● SZ**

How to order	
1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Color (Finish)

1 2 3 4
GN 300.4-92-M10-47-RS