




Specification

Lever body

Zinc die-cast

Powder coated

• Black, RAL 9005, textured finish

• Orange, RAL 2004, textured finish

• Red, RAL 3000, textured finish

• Silver, RAL 9006, textured finish

● SW

● OS

● RS

● SR

Insert / Retaining screw

Stainless steel AISI 303

RoHS

On request

• Special stud lengths and threads

Adjustable levers GN 302.1 have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...	Page
GN 302 Straight Adjustable Levers (with Steel Threaded Stud)	QVX
GN 300 Adjustable Levers (with Steel Threaded Stud)	QVX
GN 300.1 Adjustable Levers (with Stainless Steel Threaded Stud)	QVX
Technical Information	
Stainless Steel Characteristics	QVX

How to order (Inch)

1

2

3

4

GN 302.1-22-5/16X18-63-RS

1	Lever length l ₁
2	Thread d ₁
3	Thread length l ₂
4	Color

How to order (Metric)

1

2

3

4

GN 302.1-78-M10-25-SW

1	Lever length l ₁
2	Thread d ₁
3	Thread length l ₂
4	Color

www.jwwinco.com | 1-800-877-8351

 WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

1

Inch table

1 2 3

Dimensions in: inches / millimeters

I ₁	d ₁	I ₂								d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
0.87 22	6 x 32	0.24 6	0.31 8	0.39 10	0.47 12	0.63 16	-	-	-	0.31 8	0.41 10.5	0.73 18.5	0.08 2	0.65 16.5	0.12 3
0.87 22	8 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	-	-	-	0.31 8	0.41 10.5	0.73 18.5	0.08 2	0.65 16.5	0.12 3
0.87 22	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.31 8	0.41 10.5	0.73 18.5	0.08 2	0.65 16.5	0.12 3
1.18 30	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.18 30	10 x 24	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.18 30	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	10 x 32	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
2.48 63	5/16 x 18	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.97 50	2.48 63	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.97 50	-	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4

Metric table

1

2

3

Dimensions in: millimeters / inches

I ₁	d ₁			I ₂							d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke
22 0.87	M 3	-	-	6 0.24	8 0.31	10 0.39	12 0.47	16 0.63	-	-	8 0.31	10.5 0.41	18.5 0.73	2 0.08	16.5 0.65	3 0.12
22 0.87	M 4	M 5	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	8 0.31	10.5 0.41	18.5 0.73	2 0.08	16.5 0.65	3 0.12
30 1.18	M 4	-	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
30 1.18	M 5	M 6	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 4	-	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 5	M 6	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
63 2.48	M 6	M 8	-	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16
78 3.07	M 8	M 10	M 12	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16