



**SS** Stainless Steel

**3 Type**

- A** Without slot
- N** With slot

**Metric table**

**1**

**2**

Dimensions in: millimeters - inches

Length <i>l</i> ≈	d <sub>1</sub> H9 Bore	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈	h <sub>3</sub> ≈	h <sub>4</sub> ≈	t +0.5	Ø Handle	Socket cap screw DIN 912
63 2.48	B 10	18 0.71	28 1.10	18 0.71	74 2.91	40 1.57	18 0.71	18 0.71	M 5
80 3.15	B 10	18 0.71	28 1.10	18 0.71	74 2.91	40 1.57	18 0.71	18 0.71	M 5
100 3.94	B 12	20 0.79	30 1.18	20 0.79	88 3.46	50 1.97	20 0.79	21 0.83	M 6
125 4.92	B 12	20 0.79	30 1.18	20 0.79	88 3.46	50 1.97	20 0.79	21 0.83	M 6

**Specification**

- Crank body  
Stainless steel AISI 304  
Shot-blasted
- Crank arm and hub  
Butt-welded
- Cover cap  
Plastic, black
- Cylindrical revolving handle  
Plastic  
Duroplast (Phenolic PF)  
- Black, shiny finish  
- Temperature resistant up to 230 °F (110 °C)
- RoHS compliant

**Information**

GN 369.5 commercial crank handles feature a compact design and are used for light drive and adjustment tasks. Due to the materials used, these crank handles are also suitable for aggressive environments.

The slot of type N easily transfers the rotary movement to the shaft by means of a cross pin mounted on the shaft. The crank handle can be mounted removably or permanently assembled axially with a DIN 912 socket cap screw. Type A can be ordered with GN 110 cross holes.

Thanks to the simple manufacturing process it is relatively easy and inexpensive to produce customized designs of these crank handles.

see also...

- Ergostyle® Crank Handles EN 670.2 (Technopolymer Plastic)
- Crank Handles GN 471 (Aluminum)

How to order <b>GN 369.5-125-B12-A</b>	<b>1</b>	<b>Length l</b>
	<b>2</b>	<b>Bore d<sub>1</sub></b>
	<b>3</b>	<b>Type</b>