




Inch table

Dimensions in: inches / millimeters													
1	2					2							
l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.	
0.87 22	6 x 32	8 x 32	10 x 32	-	-	0.31 8	0.41 10.5	0.73 18.5	0.08 2	0.65 16.5	0.12 3	0.20 5	
1.18 30	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	0.35 9	
1.77 45	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	0.35 9	
2.48 63	1/4 x 20	5/16 x 18	-	B 1/4	B 5/16	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4	0.43 11	
3.07 78	5/16 x 18	3/8 x 16	3/8 x 24	B 5/16	B 3/8	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4	0.55 14	

Metric table

1	2			2		Dimensions in: millimeters / inches							
l ₁	d ₁ Thread			d ₂ H7 Bore		d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	t min.	
22 0.87	M 3	M 4	M 5	B 4	B 5	8 0.31	10.5 0.41	18.5 0.73	2 0.08	16.5 0.65	3 0.12	5 0.20	
30 1.18	M 3	-	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	7 0.28	
30 1.18	M 4	M 5	M 6	B 5	B 6	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35	
45 1.77	M 4	M 5	M 6	B 5	B 6	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35	
63 2.48	M 6	M 8	-	B 8	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16	11 0.43	
78 3.07	M 8	M 10	M 12	B 8	B 10	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16	14 0.55	

Specification

Lever body

Zinc die-cast

Powder coated

- Black, RAL 9005, textured finish
- Orange, RAL 2004, textured finish
- Red, RAL 3000, textured finish
- Silver, RAL 9006, textured finish

- SW
- OS
- RS
- SR

Tapped insert / Retaining Screw

Steel, blackened finish

RoHS

On request

- Special bores and threads

Technical Information

ISO Fundamental Tolerances

Page

QVX

Adjustable levers GN 302 have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

GN 302.1 Straight Adjustable Levers (with Stainless Steel Insert)

GN 300 Adjustable Levers (with Steel Insert)

Page

QVX

QVX

How to order (Inch)

GN 302-22-6X32-SW

- 1 Lever length l₁
- 2 Thread d₁ (Bore d₂)
- 3 Color

How to order (Metric)

GN 302-45-B5-SR

- 1 Lever length l₁
- 2 Bore d₂ (Thread d₁)
- 3 Color