



SS Stainless Steel

3 Type

- D With plain shaft
- E With threaded shaft

Metric table

2

Dimensions in: millimeters - inches

d ₁	d ₂ h8 Type D ST	d ₃ Type E			d ₄ h13	l ₁ ≈	l ₂	l ₃	A/F Internal hexagon (millimeter)
		ST	A4	KT					
16 .63	7 .28	M 6	M 6	-	10 .39	50 1.97	11 .43	7 .28	3
20 .79	8 .31	M 8	M 8	M 8	13 .51	64 2.52	13 .51	8 .31	4
25 .98	10 .39	M 10	M 10	M 10	16 .63	80 3.15	14 .55	10 .39	5
32 1.26	13 .51	M 12	-	M 12	20 .79	100 3.94	21 .83	13 .51	6
36 1.42	16 .63	M 16	-	-	22 .87	112 4.41	26 1.02	14 .55	8

Specification

1

- Steel **ST**
Zinc plated, blue passivated finish
- Stainless steel **A4**
European Standard No. 1.4404 (AISI 316L)
- Plastic **KT**
Technopolymer (Polyamide PA)
 - Temperature resistant up to 213 °F (100 °C)
 - Black, matte finish
 - Steel threaded shaft, blackened finish, molded-in

• RoHS compliant

Information

DIN 39 fixed handles are used in applications where a positive non-revolving grip is required. For hygienic reasons, a hexagonal recess is not used in type A4.

How to order DIN 39-ST-25-E	1	Material
	2	Handle diameter d ₁
	3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4