


Application example



Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Thread	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄ Stroke	s	t min.
30 1.18	M 5	13 0.51	10 0.39	13 0.51	24.5 0.96	4 0.16	31 1.22	3.5 0.14	2.5 0.10	10 0.39
45 1.77	M 6	15 0.59	10 0.39	13 0.51	24.5 0.96	4 0.16	34 1.34	3.5 0.14	3 0.12	10 0.39
63 2.48	M 8	20 0.79	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	45 1.77	4 0.16	3.5 0.14	13 0.51
78 3.07	M 10	25 0.98	16 0.63	21 0.83	36 1.42	8 0.31	54 2.13	4 0.16	4 0.16	16 0.63

Specification

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Orange, RAL 2004, textured finish **● OS**
 - Red, RAL 3000, textured finish **● RS**
 - Silver, RAL 9006, textured finish **● SR**
- Tapped insert / retaining screw
Steel, blackened finish
- Washer
Steel
 - Case hardened
 - Blackened finish
- RoHS compliant

Information

GN 307 adjustable levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The washer cannot be removed and does not turn when the lever is actuated. It protects the clamped surface from damage. One typical application is to use the hand lever for slotted holes.

see also...

- Adjustable Levers GN 300 (without Washer) → page QVX
- Adjustable Levers GN 300.4 (with Increased Clamping Force) → page QVX
- Adjustable Levers GN 303 (with Push Button) → page QVX

How to order	¹ ² ³	1 Lever length l ₁
		2 Thread d ₁
		3 Color
GN307-63-M8-SW		