



Metric table

Dimensions in: millimeters - inches

1	2	3																		
l_1	d_1	l_2	d_2	d_3	d_4	l_3	h_1	h_2	h_3	h_4	s									
										Stroke										
30 1.18	M 5	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	13 0.51	10 0.39	13 0.51	0.4 0.02	24.5 0.96	4 0.16	31 1.22	3.5 0.14	2.5 0.10					
45 1.77	M 6	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	15 0.59	10 0.39	13 0.51	0.4 0.02	24.5 0.96	4 0.16	34 1.34	3.5 0.14	3 0.12					
63 2.48	M 8	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	20 0.79	13.5 0.53	17.5 0.69	0.4 0.02	31 1.22	6.5 0.26	45 1.77	4 0.16	3.5 0.14					
78 3.07	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	25 0.98	16 0.63	21 0.83	0.5 0.02	36 1.42	12 0.47	54 2.13	4 0.16	4 0.16					

Specification

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish **SW**
 - Orange, RAL 2004, textured finish **OS**
 - Red, RAL 3000, textured finish **RS**
 - Silver, RAL 9006, textured finish **SR**
- Threaded stud / retaining screw
 - Steel
 - Property class 5.8
 - Blackened finish
- Washer
 - Steel
 - Case hardened
 - Blackened finish
- Strength Values of Screws → page QVX
- RoHS compliant

Information

GN 307 adjustable levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The washer cannot be removed and does not turn when the lever is actuated. It protects the clamped surface from damage. One typical application is to use the hand lever for slotted holes.

see also...

- Adjustable Levers GN 300 (without Washer) → page QVX
- Adjustable Levers GN 300.4 (with Increased Clamping Force) → page QVX
- Adjustable Levers GN 303 (with Push Button) → page QVX

How to order	1	Lever length l_1
	2	Thread d_1
	3	Thread length l_2
	4	Color

GN 307-45-M6-25-SW