



ELESA original design MMT.

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> l <sub>1</sub> ±0.5	l <sub>2</sub>	b	d <sub>2</sub> Thread	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	t min.
10 .39	120 4.72	94 3.70	16 .63	M 5	18 .71	53 2.09	43 1.69	8 .31	24 .94	12 .47
10 .39	180 7.09	94 3.70	16 .63	M 5	18 .71	56 2.20	43 1.69	8 .31	24 .94	12 .47

**Specification**

- Steel, matte chrome-plated finish
- Grip  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 302 °F (150 °C)  
- Black, matte finish
- RoHS compliant

**Information**

EN 425.7 cabinet “U” handles made of steel feature a plastic grip which, owing to its insulating properties, allows it to be used under high surface temperatures.

The above temperature distribution curve has been measured at a surface temperature of 392 °F (200 °C) and a room temperature of 73 °F (23 °C).

see also...

- Cabinet “U” Handles GN 425 (Steel)

How to order <sup>1</sup> <sup>2</sup> <b>EN 425.7-10-120</b>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Length l <sub>1</sub>