



- 3 Type**
- A** Mounting from the back (tapped blind hole)
 - B** Mounting from the operator's side (only for $d_1 = 28$ mm)

Inch table

Dimensions in: inches - *millimeters*

d₁	l₁ ±0.01						d₂ Thread	b₁	b₂	h₁	h₂	t min.
0.79 20.1	7.00 177.8	8.00 203.2	10.00 254.0	12.00 304.8	16.00 406.4	-	1/4 x 20	0.94 23.9	0.47 11.9	1.97 50.0	2.60 66.0	0.59 15.0
1.10 27.9	8.00 203.2	10.00 254.0	12.00 304.8	16.00 406.4	20.00 508.0	24.00 609.6	5/16 x 18	0.98 24.9	0.98 24.9	1.97 50.0	2.60 66.0	0.59 15.0

Metric table

Dimensions in: millimeters - *inches*

d₁	l₁ ±0.25							d₂ Thread	d₃ Thread	b₁	b₂	h₁	h₂	h₃	l₂ max.	l₃	t min.
20 0.79	180 7.09	200 7.87	250 9.84	300 11.81	350 13.78	400 15.75	-	M 6	-	24 0.94	12 0.47	42 1.65	54 2.13	-	-	-	12 0.47
28 1.10	200 7.87	250 9.84	300 11.81	350 13.78	400 15.75	500 19.69	600 23.62	M 8	M 6	25 0.98	14 0.55	50 1.97	66 2.60	7 0.28	6 0.24	13 0.51	15 0.59
30 1.18	200 7.87	300 11.81	350 13.78	400 15.75	500 19.69	600 23.62	1000 39.37	M 8	-	27 1.06	17 0.67	51 2.01	68 2.68	-	-	-	15 0.59

Specification

- Tube
Aluminum (wall thickness 1.5 mm)
- Handle legs
Zinc die-cast, powder coated
- Tube / handle legs **SW**
Powder coated
Black, RAL 9005, textured finish
- Tube **EL**
Anodized finish, natural color
Handle legs
Black, RAL 9005, textured finish
- Tube **ES**
Anodized finish, natural color
Handle legs
Silver RAL 9006, textured finish
- Covers
Plastic, light gray
- Type B
 - Socket button head screws ISO 7380-M6-20
 - Hexagon nuts ISO 4032-M6
 - Washers DIN 125
 Steel, zinc plated, blue passivated finish
- Load Rating Information → page 2068
- RoHS compliant

Information

The handle tube of the GN 333.1 tubular handles can be screwed to the handle bases without further machining or processing, allowing special lengths to be realised easily.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles Ø 28 (type A) are available under GN 333.9.

For type B, socket button head screws, hexagon nuts and washers are included.

see also...

- Product Family Standard Parts for Profile Systems → page 18
- Tubular Handles GN 333 (with Angled Legs) → page 168
- Tubular Handles GN 333.7 (Stainless Steel) → page 165
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems) → page 2048
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems) → page 2058

Accessory

- Straight handle legs GN 333.9 → www.jwwinco.com

How to order	1 Handle diameter d_1
	2 Length l
	3 Type
	4 Finish

1
2
3
4
GN 333.1-0.79-12.00-A-ES