


Metric



4 Type

- A** With handle held in the folded up or folded down position
- B** With spring return of the handle to the folded down position

Metric table



Dimensions in: millimeters / inches

l_1	l_2	l_3	l_4	l_5	l_6	m_1	m_2
100 3.94	150 5.91	65 2.56	121 4.76	122 4.80	60 2.36	134 5.28	49 1.93
120 4.72	170 6.69	65 2.56	141 5.55	142 5.59	60 2.36	154 6.06	49 1.93

Specification



Folding handle

- Steel, chrome plated finish
- Stainless steel AISI 303
- Matte shot-blasted finish

CR
NI

Tray

- Zinc die-cast
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

● **SW**
● **SR**

RoHS

Folding handles GN 425.8 with recessed tray are used in applications where the handle must not protrude more than 3 mm when in the folded down position.

The recessed tray gives this handle added strength. Folding handle and recessed tray are supplied as a complete assembly.

In type A, the handle is held in both the folded up and folded down position by means of a spring-loaded (spring disks) thrust bolt.

In type B, the handle always springs back to the folded down position after being released, preventing it from protruding at undesirable times.

see also...

	Page
EN 825.2 Folding Handles with Recessed Tray (Plastic, with Spring-Loaded Return)	QVX
EN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Installation Dimensions	QVX
Load Capacity Information	QVX
Stainless Steel Characteristics	QVX

How to order

1 Length l_1
2 Finish / material handle
3 Finish tray
4 Type

GN 425.8-120-CR-SW-A

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4





Installation Dimensions

