



2 Type

- A Mounting from the back (tapped blind hole)

Metric table

1

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	t min.
28 1.10	M 8	25 0.98	14 0.55	50 1.97	66 2.60	50 1.97	66 2.60	15 0.59

Specification

3

- Zinc die-cast
Powder coated
Black, RAL 9005, textured finish
Silver, RAL 9006, textured finish
- Set screw with plastic tip
GN 913.3-M4-6-KU → page QVX
- RoHS compliant

- SW
- SR

Information

GN 333.8 and GN 333.9 handle legs are highly stable in relation to their small dimensions. They can be used with longer tubes or higher loads when combined with the same 28 mm diameter tube used for the GN 333, GN 333.1, GN 333.2 and GN 333.3 tubular handles.

Handle legs secure to tube via set screws. They are mounted to the surface from the bottom, utilizing a tapped blind hole.

see also...

- Tubular Handles GN 333 (with Angled Legs) → page QVX
- Tubular Handles GN 333.1 (with Straight Legs) → page QVX
- Tubular Handles GN 333.2 (with Angled Movable Legs) → page QVX
- Tubular Handles GN 333.3 (with Straight Movable Legs) → page QVX

How to order (Angled)	1 Handle diameter d ₁
GN 333.8-28-A-SW	2 Type
	3 Finish

How to order (Straight)	1 Handle diameter d ₁
GN 333.9-28-A-SR	2 Type
	3 Finish