

- 4 Type (Base)**
- A0** Without rubber pad / cap
 - A1** With rubber cap, clipped on, black
 - A3** With rubber pad, vulcanized, black

Inch table

Dimensions in: inches - millimeters

1 d₁	2 d₂ Thread	3 l₁ Version S / SK				Version U / UK				3 l₇ Version X	d₃	h₁	h₆	l₈	m	r	s
1.97 50	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
2.36 60	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	1.02 26	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.14 29	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.50 38	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	1.77 45	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2

d ₁	d ₂ Thread	h ₃	h ₄	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
1.97 50	5/16 x 18	-	-	-	-	-	0.55 14	0.31 8
1.97 50	3/8 x 16	0.43 11	-	0.67 17	-	-	0.55 14	0.39 10
1.97 50	1/2 x 13	0.43 11	-	0.67 17	-	-	0.67 17	0.47 12
1.97 50	5/8 x 11	-	0.67 17	-	0.47 12	0.31 8	0.87 22	0.63 16
2.36 60	5/16 x 18	-	-	-	-	-	0.55 14	0.31 8
2.36 60	3/8 x 16	0.43 11	-	0.67 17	-	-	0.55 14	0.39 10
2.36 60	1/2 x 13	0.43 11	-	0.67 17	-	-	0.67 17	0.47 12
2.36 60	5/8 x 11	-	0.67 17	-	0.47 12	0.31 8	0.87 22	0.63 16
3.15 80	5/16 x 18	-	-	-	-	-	0.55 14	0.31 8
3.15 80	3/8 x 16	0.47 12	-	0.67 17	-	-	0.55 14	0.39 10
3.15 80	1/2 x 13	0.47 12	-	0.67 17	-	-	0.67 17	0.47 12
3.15 80	5/8 x 11	-	0.71 18	-	0.47 12	0.31 8	0.87 22	0.63 16
3.15 80	3/4 x 10	-	0.75 19	-	0.59 15	0.39 10	1.06 27	0.79 20

3.1

3.2

3.3

3.4

3.5

3.6




3.7

3.8

3.9

3.10



Stud / socket versions		
 <p>S Without nut SK With nut</p>	 <p>U Without nut UK With nut</p>	 <p>X Tapped socket type</p>
<p>External hexagon at the bottom at d_2 3/8 x 16, 1/2 x 13 M 8, M 10, M 12</p>	<p>Internal hexagon at the top, wrench flat at the bottom at d_2 5/8 x 11, 3/4 x 10 M 16, M 20, M 24</p>	<p>External hexagon with tapped socket at d_2 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20</p>

Metric table

d_1	d_2 Thread	l_1 Version S / SK										l_7 Version X	d_3	h_1	h_6	l_8	m	r	s
		Version S / SK						Version U / UK											
50	M 8	40	50	63	-	-	-	-	-	-	25	13	2.5	4	60	45	15	2	
1.97		1.57	1.97	2.48							0.98	0.51	0.10	0.16	2.36	1.77	0.59	0.08	
50	M 10	50	60	80	100	-	-	-	-	-	28	13	2.5	4	60	45	15	2	
1.97		1.97	2.36	3.15	3.94						1.10	0.51	0.10	0.16	2.36	1.77	0.59	0.08	
50	M 12	60	80	100	125	-	-	-	-	-	32	13	2.5	4	60	45	15	2	
1.97		2.36	3.15	3.94	4.92						1.26	0.51	0.10	0.16	2.36	1.77	0.59	0.08	
50	M 16	-	-	-	-	75	100	125	150	200	37	13	2.5	4	60	45	15	2	
1.97						2.95	3.94	4.92	5.91	7.87	1.46	0.51	0.10	0.16	2.36	1.77	0.59	0.08	
60	M 8	40	50	63	-	-	-	-	-	-	25	13	2.5	4.5	65	50	15	2	
2.36		1.57	1.97	2.48							0.98	0.51	0.10	0.18	2.56	1.97	0.59	0.08	
60	M 10	50	60	80	100	-	-	-	-	-	28	13	2.5	4.5	65	50	15	2	
2.36		1.97	2.36	3.15	3.94						1.10	0.51	0.10	0.18	2.56	1.97	0.59	0.08	
60	M 12	60	80	100	125	-	-	-	-	-	32	13	2.5	4.5	65	50	15	2	
2.36		2.36	3.15	3.94	4.92						1.26	0.51	0.10	0.18	2.56	1.97	0.59	0.08	
60	M 16	-	-	-	-	75	100	125	150	200	37	13	2.5	4.5	65	50	15	2	
2.36						2.95	3.94	4.92	5.91	7.87	1.46	0.51	0.10	0.18	2.56	1.97	0.59	0.08	
80	M 8	40	50	63	-	-	-	-	-	-	26	13	3	5	85	70	15	2	
3.15		1.57	1.97	2.48							1.02	0.51	0.12	0.20	3.35	2.76	0.59	0.08	
80	M 10	50	60	80	100	-	-	-	-	-	29	13	3	5	85	70	15	2	
3.15		1.97	2.36	3.15	3.94						1.14	0.51	0.12	0.20	3.35	2.76	0.59	0.08	
80	M 12	60	80	100	125	-	-	-	-	-	32	13	3	5	85	70	15	2	
3.15		2.36	3.15	3.94	4.92						1.26	0.51	0.12	0.20	3.35	2.76	0.59	0.08	
80	M 16	-	-	-	-	75	100	125	150	200	38	13	3	5	85	70	15	2	
3.15						2.95	3.94	4.92	5.91	7.87	1.50	0.51	0.12	0.20	3.35	2.76	0.59	0.08	
80	M 20	-	-	-	-	75	100	125	150	200	45	13	3	5	85	70	15	2	
3.15						2.95	3.94	4.92	5.91	7.87	1.77	0.51	0.12	0.20	3.35	2.76	0.59	0.08	
80	M 24	-	-	-	-	100	125	150	200	-	-	13	3	5	85	70	15	2	
3.15						3.94	4.92	5.91	7.87			0.51	0.12	0.20	3.35	2.76	0.59	0.08	

d ₁	d ₂ Thread	h ₃	h ₄	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
50 1.97	M 8	11 0.43	-	17 0.67	-	-	14 0.55	8 0.31
50 1.97	M 10	11 0.43	-	17 0.67	-	-	14 0.55	10 0.39
50 1.97	M 12	11 0.43	-	17 0.67	-	-	17 0.67	12 0.47
50 1.97	M 16	-	17 0.67	-	12 0.47	8 0.31	22 0.87	16 0.63
60 2.36	M 8	11 0.43	-	17 0.67	-	-	14 0.55	8 0.31
60 2.36	M 10	11 0.43	-	17 0.67	-	-	14 0.55	10 0.39
60 2.36	M 12	11 0.43	-	17 0.67	-	-	17 0.67	12 0.47
60 2.36	M 16	-	17 0.67	-	12 0.47	8 0.31	22 0.87	16 0.63
80 3.15	M 8	12 0.47	-	17 0.67	-	-	14 0.55	8 0.31
80 3.15	M 10	12 0.47	-	17 0.67	-	-	14 0.55	10 0.39
80 3.15	M 12	12 0.47	-	17 0.67	-	-	17 0.67	12 0.47
80 3.15	M 16	-	18 0.71	-	12 0.47	8 0.31	22 0.87	16 0.63
80 3.15	M 20	-	19 0.75	-	15 0.59	10 0.39	27 1.06	20 0.79
80 3.15	M 24	-	22 0.87	-	19 0.75	12 0.47	-	-

Specification

- Base
Steel, zinc plated, blue passivated finish
- Threaded stud / tapped socket
Steel, zinc plated, blue passivated finish
- Hexagon nut ISO 4032
Steel, zinc plated, blue passivated finish
- Rubber cap
Santoprene® (TPE) ≈ 80 shore A
- Clipped on
- Black
- Rubber pad
Perbunan® (NBR) 70 ±5 shore A
- Vulcanized, non-skid
- Black
- RoHS compliant

Information

GN 42 leveling feet are simple, economically priced components and can be used universally thanks to the wide range of possible combinations of the base and the adjusting spindle variations.


The leveling feet can be screwed to the mounting surface using the lag bolt hole, which prevents lateral slippage. The types with rubber pad / cap also protect sensitive surfaces.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 40 (Steel, without Lag Bolt Hole)
- Leveling Feet GN 42 (Steel, with Slotted Lag Bolt Hole, Rectangular Shape)
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Lag Bolt Hole)
- Leveling Feet GN 44 / GN 45
(Stainless Steel AISI 316, with / without Lag Bolt Hole)
- Threaded Tube Ends EN 448 (Plastic)
- Threaded Tube Inserts GN 992 (Aluminum)

<p>How to order (Inch)</p>  <p>GN 42-50-3/8X16-75-A0-S</p>	1	Base diameter d ₁
	2	Thread d ₂
	3	Length l ₁ (Length l ₇)
	4	Type (Base)
	5	Stud / socket version

<p>How to order (Metric)</p>  <p>GN 42-80-M10-29-A1-X</p>	1	Base diameter d ₁
	2	Thread d ₂
	3	Length l ₇ (Length l ₁)
	4	Type (Base)
	5	Stud / socket version

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

