



Metric table

Dimensions in: millimeters - inches

1 b	2 d Thread	3 l ₁ ±0.5	a	h	l ₂	l ₃	l ₄	t min.
36 1.42	M 6 M 8	200 7.87	24 .94	57 2.24	236 9.29	164 6.46	290 11.42	15 .59
36 1.42	M 6 M 8	250 9.84	24 .94	57 2.24	286 11.26	214 8.43	340 13.39	15 .59
36 1.42	M 6 M 8	300 11.81	24 .94	57 2.24	336 13.23	264 10.39	390 15.35	15 .59
36 1.42	M 6 M 8	400 15.75	24 .94	57 2.24	436 17.17	364 14.33	490 19.29	15 .59
36 1.42	M 6 M 8	500 19.69	24 .94	57 2.24	536 21.10	464 18.27	590 23.23	15 .59
36 1.42	M 6 M 8	600 23.62	24 .94	57 2.24	636 25.04	564 22.20	690 27.17	15 .59

Specification

- Tube
Aluminum
- Handle legs / covers
Plastic, Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Tube **SW**
Powder coated
Black, RAL 9005, textured finish
Handle legs / covers
Black, matte finish
- Tube **ELS**
Anodized finish, natural color
Handle legs / covers
Black, matte finish
- Tube **ELG**
Anodized finish, natural color
Handle legs / covers
Light gray, matte finish
- Tapped inserts
Steel, zinc plated
- RoHS compliant

Information

Unique to the design of the GN 366 tubular handles is that the tube and the handle legs are in the same elliptical profile.
see also...
• *Oval Tubular Handles GN 334 (Mounting from the Back)*

On request

- Special tube lengths other than listed

How to order

GN 366-36-M8-400-ELS

1	Handle diameter b
2	Thread d
3	Length l ₁
4	Finish