



Metric table

Dimensions in: millimeters - inches

1 b	2 d Thread	3 l ₁ ±0.5	a	h	l ₂	l ₃	l ₄	t min.
36 1.42	M 6 M 8	200 7.87	24 0.94	57 2.24	236 9.29	164 6.46	290 11.42	15 0.59
36 1.42	M 6 M 8	250 9.84	24 0.94	57 2.24	286 11.26	214 8.43	340 13.39	15 0.59
36 1.42	M 6 M 8	300 11.81	24 0.94	57 2.24	336 13.23	264 10.39	390 15.35	15 0.59
36 1.42	M 6 M 8	400 15.75	24 0.94	57 2.24	436 17.17	364 14.33	490 19.29	15 0.59
36 1.42	M 6 M 8	500 19.69	24 0.94	57 2.24	536 21.10	464 18.27	590 23.23	15 0.59
36 1.42	M 6 M 8	600 23.62	24 0.94	57 2.24	636 25.04	564 22.20	690 27.17	15 0.59

Specification

- Tube
Aluminum
- Handle legs / covers
Plastic, Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Tube **SW**
Powder coated
Black, RAL 9005, textured finish
Handle legs / covers
Black, matte finish
- Tube **ELS**
Anodized finish, natural color
Handle legs / covers
Black, matte finish
- Tube **ELG**
Anodized finish, natural color
Handle legs / covers
Light gray, matte finish
- Tapped inserts
Steel, zinc plated
- *Load Rating Information* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

On request

- Special tube lengths other than listed

Information

Unique to the design of the GN 366 tubular handles is that the tube and the handle legs are in the same elliptical profile.

see also...

- *Oval Tubular Handles GN 334 (Mounting from the Back)* → page QVX

How to order

GN 366-36-M8-400-ELS

- 1** Handle diameter b
- 2** Thread d
- 3** Length l₁
- 4** Finish