


SS Stainless Steel

4 Type (Base)

- E0** Without rubber pad, with 1 slotted hole
- E3** With rubber pad, vulcanized, black, with 1 slotted hole
- G0** Without rubber pad, with 2 slotted holes
- G3** With rubber pad, vulcanized, black, with 2 slotted holes









Inch table

Dimensions in: inches - millimeters

d <sub>1</sub>	d <sub>2</sub> Thread	1				2				l <sub>7</sub> Version X	
		3		3		3		3			
		Version S / SK				Version U / UK					
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	-	1.02 26
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	-	1.14 29
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	-	1.26 32
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	-	1.50 38
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	-	1.77 45

d <sub>1</sub>	d <sub>2</sub> Thread	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>6</sub>	l <sub>8</sub>	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>7</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	r	t
3.15 80	5/16 x 18	0.51 13	0.41 10.5	0.12 3	0.05 1.3	0.47 12	-	0.12 3	2.76 70	0.67 17	-	-	0.55 14	1.06 27	1.02 26	1.97 50	0.59 15	0.31 8
3.15 80	3/8 x 16	0.51 13	0.41 10.5	0.12 3	0.05 1.3	0.47 12	-	0.12 3	2.76 70	0.67 17	-	-	0.55 14	1.06 27	1.02 26	1.97 50	0.59 15	0.39 10
3.15 80	1/2 x 13	0.51 13	0.41 10.5	0.12 3	0.05 1.3	0.47 12	-	0.12 3	2.76 70	0.67 17	-	-	0.67 17	1.06 27	1.02 26	1.97 50	0.59 15	0.47 12
3.15 80	5/8 x 11	0.51 13	0.41 10.5	0.12 3	0.05 1.3	-	0.71 18	0.12 3	2.76 70	-	0.47 12	0.31 8	0.87 22	1.06 27	1.02 26	1.97 50	0.59 15	0.63 16
3.15 80	3/4 x 10	0.51 13	0.41 10.5	0.12 3	0.05 1.3	-	0.75 19	0.12 3	2.76 70	-	0.59 15	0.39 10	1.06 27	1.06 27	1.02 26	1.97 50	0.59 15	0.79 20

Stud / socket versions		
 <p><b>5</b> <b>S</b> Without nut <b>SK</b> With nut</p>	 <p><b>5</b> <b>T*</b> Without nut <b>TK*</b> With nut</p>	 <p><b>5</b> <b>U</b> Without nut <b>UK</b> With nut</p>
External hexagon at the bottom at $d_2$ 3/8 x 16, 1/2 x 13 M 8, M 10, M 12	Wrench flat at the bottom at $d_2$ - M 16, M 20, M 24	Internal hexagon at the top, wrench flat at the bottom at $d_2$ 5/8 x 11, 3/4 x 10 M 16, M 20, M 24
 <p><b>5</b> <b>V*</b> Without nut <b>VK*</b> With nut</p>	 <p><b>5</b> <b>W*</b> With adjustable sleeve</p>	 <p><b>5</b> <b>X</b> Tapped socket type</p>
External hexagon at the top, wrench flat at the bottom at $d_2$ - M 16	Covered thread, wrench flat at the bottom at $d_2$ - M 16	External hexagon with tapped socket at $d_2$ 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20

\* Only available with Metric thread

**Metric table**

Dimensions in: millimeters - inches

<b>1</b>	<b>2</b>	<b>3</b>		<b>3</b>								<b>3</b>				<b>3</b>			
$d_1$	$d_2$	$l_1$		$l_2$								$l_3$				$l_7$			
Thread	Version S / SK	Version T / TK and U / UK								Version V / VK				Version W				Version X	
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	26 1.02
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	29 1.14
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	38 1.50
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	-	-	-	-	-	-	-	-	45 1.77
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	-	-	-	-	-	-	-	-	-	-

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10



d <sub>1</sub>	d <sub>2</sub> Thread	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>5</sub>	h <sub>6</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>	l <sub>8</sub>
80 3.15	M 8	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	12 0.47	-	-	3 0.12	-	-	-	70 2.76
80 3.15	M 10	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	12 0.47	-	-	3 0.12	-	-	-	70 2.76
80 3.15	M 12	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	12 0.47	-	-	3 0.12	-	-	-	70 2.76
80 3.15	M 16	13 0.51	10.5 0.41	24 0.94	3 0.12	1.3 0.05	-	18 0.71	15 0.59	3 0.12	45 1.77	45 1.77	29 1.14	70 2.76
80 3.15	M 20	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	-	19 0.75	-	3 0.12	-	-	-	70 2.76
80 3.15	M 24	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	-	22 0.87	-	3 0.12	-	-	-	70 2.76

d <sub>1</sub>	d <sub>2</sub> Thread	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>4</sub>	A/F <sub>5</sub>	A/F <sub>6</sub>	A/F <sub>7</sub>	m <sub>1</sub>	m <sub>2</sub>	m <sub>3</sub>	r	t
80 3.15	M 8	17 0.67	-	-	-	-	-	14 0.55	27 1.06	26 1.02	50 1.97	15 0.59	8 0.31
80 3.15	M 10	17 0.67	-	-	-	-	-	14 0.55	27 1.06	26 1.02	50 1.97	15 0.59	10 0.39
80 3.15	M 12	17 0.67	-	-	-	-	-	17 0.67	27 1.06	26 1.02	50 1.97	15 0.59	12 0.47
80 3.15	M 16	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	27 1.06	26 1.02	50 1.97	15 0.59	16 0.63
80 3.15	M 20	-	15 0.59	10 0.39	-	-	-	27 1.06	27 1.06	26 1.02	50 1.97	15 0.59	20 0.79
80 3.15	M 24	-	19 0.75	12 0.47	-	-	-	-	27 1.06	26 1.02	50 1.97	15 0.59	-

**Specification**

- Base  
Stainless steel, plain, tumbled finish  
European Standard No. 1.4301 (AISI 304)
- Threaded stud / tapped socket  
Stainless steel  
European Standard No. 1.4305 (AISI 303)
- Hexagon nut ISO 4032  
Stainless steel  
European Standard No. 1.4301 (AISI 304)
- Rubber pad  
Perbunan® (NBR) 70 ±5 shore A  
- Vulcanized, non-skid  
- Black
- RoHS compliant

**Information**


GN 43 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the adjusting spindle variations make these leveling feet universally applicable.


The leveling feet can be screwed to the mounting surface using the slotted lag bolt hole, which prevents lateral slippage. The types with rubber pad also protect sensitive surfaces.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 40 (Steel, without Fixing Lug)
- Leveling Feet GN 42 (Steel, with Fixing Lug)
- Leveling Feet GN 42 (Steel, with Slotted Lag Bolt Hole, Rectangular Shape)
- Leveling Feet GN 41 (Stainless Steel AISI 304, without Fixing Lug)
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Fixing Lug) →
- Leveling Feet GN 44 / GN 45 (Stainless Steel AISI 316, with / without Fixing Lug)
- Threaded Tube Ends EN 448 (Plastic)
- Threaded Tube Inserts GN 992.5 (Stainless Steel)

<p>How to order (Inch)</p>  <p>GN 43-80-3/8X16-75-E0-S</p>	1	Base diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Length l <sub>1</sub> (Length l <sub>7</sub> )
	4	Type (Base)
	5	Stud / socket version

<p>How to order (Metric)</p>  <p>GN 43-80-M16-100-G3-UK</p>	1	Base diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Length l <sub>1</sub> (Length l <sub>2</sub> , l <sub>3</sub> , l <sub>7</sub> )
	4	Type (Base)
	5	Stud / socket version