



- 3 Type**
- A Without slot
 - N With slot

Metric table

Dimensions in: millimeters - inches

| Length 1 l | Bore 2 d_1 H9 | d_2 | h_1 | $h_2 \approx$ | $h_3 \approx$ | $h_4 \approx$ | $t +0.5$ | Ø Handle | DIN 912 |
|--------------------------|------------------------|-----------|------------|---------------|---------------|---------------|-----------|-----------|---------|
| 63 2.48 | B 10 | 18 .71 | 28 1.10 | 18 .71 | 74 2.91 | 40 1.57 | 18 .71 | 18 .71 | M5 |
| 80 3.15 | B 10 | 18 .71 | 28 1.10 | 18 .71 | 74 2.91 | 40 1.57 | 18 .71 | 18 .71 | M5 |
| 100 3.94 | B 12 | 20 .79 | 30 1.18 | 20 .79 | 88 3.46 | 50 1.97 | 20 .79 | 21 .83 | M6 |
| 125 4.92 | B 12 | 20 .79 | 30 1.18 | 20 .79 | 88 3.46 | 50 1.97 | 20 .79 | 21 .83 | M6 |

Specification

- Crank body
Steel, sandblasted and nickel plated
- Crank arm and hub
Butt-welded
- Plastic cap
Black
- Revolving handles GN 598
 - Plastic, Duroplast
Black, glossy finish
 - Threaded spindle
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

GN 369 commercial crank handles are a good choice for light duty applications. Due to the manufacturing process, these crank handles are a more economically priced option.

see also...

- Ergostyle® Crank Handles EN 670.2 (Technopolymer Plastic)

On request

- Other modifications such as inch and special metric bores, keyways, cross holes, etc.

| | | |
|--|----------|------------------------------|
| How to order GN 369-63-B10-A | 1 | Length l |
| | 2 | Bore d_1 |
| | 3 | Type |