

SS Stainless Steel







4 Type (Base)

- D0** Without rubber pad / cap
- D1** With rubber cap, clipped on, black
- D3** With rubber pad, vulcanized, black

Inch table

1	2	3								3	Dimensions in: inches - millimeters						
		Version S / SK				Version U / UK					Version X	d ₃	h ₁	h ₆	l ₈	m	r
d ₁	d ₂ Thread	l ₁				l ₇				d ₃	h ₁	h ₆	l ₈	m	r	s	
1.97 50	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
2.36 60	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	1.02 26	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.14 29	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.50 38	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	1.77 45	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2

d ₁	d ₂ Thread	h ₃	h ₄	h ₅	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
1.97 50	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
1.97 50	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
1.97 50	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
1.97 50	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
2.36 60	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
2.36 60	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
2.36 60	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
2.36 60	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
3.15 80	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
3.15 80	3/8 x 16	0.47 12	-	-	11/16	-	-	1/2	0.39 10
3.15 80	1/2 x 13	0.47 12	-	-	11/16	-	-	5/8	0.47 12
3.15 80	5/8 x 11	-	0.71 18	0.59 15	-	1/2	5/16	7/8	0.63 16
3.15 80	3/4 x 10	-	0.75 19	0.59 15	-	9/16	7/16	1	0.79 20

Stud / socket versions		
 <p>5 S Without nut SK With nut</p>	 <p>5 T* Without nut TK* With nut</p>	 <p>5 U Without nut UK With nut</p>
<p>External hex at the bottom at d₂ 3/8 x 16, 1/2 x 13 M 8, M 10, M 12</p>	<p>Wrench flat at the bottom at d₂ - M 16, M 20, M 24</p>	<p>Internal hex at the top, wrench flat at the bottom at d₂ 5/8 x 11, 3/4 x 10 M 16, M 20, M 24</p>
 <p>5 V* Without nut VK* With nut</p>	 <p>5 W* With adjustable sleeve</p>	 <p>5 X Tapped socket type</p>
<p>External hex at the top, wrench flat at the bottom at d₂ - M 16, M 20, M 24</p>	<p>Covered thread, wrench flat at the bottom at d₂ - M 16, M 20, M 24</p>	<p>External hex with tapped socket at d₂ 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20</p>

* Only available with Metric thread

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10



Metric table

Dimensions in: millimeters - *inches*

¹ d ₁	² d ₂	³ l ₁	Version S / SK				Version T / TK and U / UK						³ l ₂ Version V / VK				³ l ₃ Version W				³ l ₇ Version X
50 1.97	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98	
50 1.97	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10	
50 1.97	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
50 1.97	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-	-	-	-	-	-	-	-	37 1.46	
60 2.36	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98	
60 2.36	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10	
60 2.36	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
60 2.36	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	37 1.46	
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	26 1.02	
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	29 1.14	
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	38 1.50	
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	100 3.94	125 4.92	150 5.91	200 7.87	134 5.28	159 6.26	184 7.24	234 9.21	45 1.77	
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	100 3.94	150 5.91	200 7.87	-	159 6.26	209 8.23	259 10.20	-	-	

d ₁	d ₂ Thread	d ₃	d ₅	h ₁	h ₃	h ₄	h ₅	h ₆	l ₄	l ₅	l ₆	l ₈	A/F ₁	A/F ₂	A/F ₃	A/F ₄	A/F ₅	A/F ₆	A/F ₇	m	r	s	t
50 1.97	M 8	13 0.51	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	60 2.36	17 0.67	-	-	-	-	-	14 0.55	45 1.77	15 0.59	2 0.08	8 0.31
50 1.97	M 10	13 0.51	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	60 2.36	17 0.67	-	-	-	-	-	14 0.55	45 1.77	15 0.59	2 0.08	10 0.39
50 1.97	M 12	13 0.51	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	60 2.36	17 0.67	-	-	-	-	-	17 0.67	45 1.77	15 0.59	2 0.08	12 0.47
50 1.97	M 16	13 0.51	-	2.5 0.10	-	17 0.67	14 0.55	4 0.16	-	-	-	60 2.36	-	12 0.47	8 0.31	-	-	-	22 0.87	45 1.77	15 0.59	2 0.08	16 0.63
60 2.36	M 8	13 0.51	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	65 2.56	17 0.67	-	-	-	-	-	14 0.55	50 1.97	15 0.59	2 0.08	8 0.31
60 2.36	M 10	13 0.51	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	65 2.56	17 0.67	-	-	-	-	-	14 0.55	50 1.97	15 0.59	2 0.08	10 0.39
60 2.36	M 12	13 0.51	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	65 2.56	17 0.67	-	-	-	-	-	17 0.67	50 1.97	15 0.59	2 0.08	12 0.47
60 2.36	M 16	13 0.51	24 0.94	2.5 0.10	-	17 0.67	14 0.55	4.5 0.18	45 1.77	45 1.77	29 1.14	65 2.56	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	50 1.97	15 0.59	2 0.08	16 0.63
80 3.15	M 8	13 0.51	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	85 3.35	17 0.67	-	-	-	-	-	14 0.55	70 2.76	15 0.59	2 0.08	8 0.31
80 3.15	M 10	13 0.51	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	85 3.35	17 0.67	-	-	-	-	-	14 0.55	70 2.76	15 0.59	2 0.08	10 0.39
80 3.15	M 12	13 0.51	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	85 3.35	17 0.67	-	-	-	-	-	17 0.67	70 2.76	15 0.59	2 0.08	12 0.47
80 3.15	M 16	13 0.51	24 0.94	3 0.12	-	18 0.71	15 0.59	5 0.20	45 1.77	45 1.77	29 1.14	85 3.35	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	70 2.76	15 0.59	2 0.08	16 0.63
80 3.15	M 20	13 0.51	30 1.18	3 0.12	-	18 0.71	15 0.59	5 0.20	56 2.20	56 2.20	37 1.46	85 3.35	-	15 0.59	10 0.39	13 0.51	16 0.63	24 0.94	27 1.06	70 2.76	15 0.59	2 0.08	20 0.79
80 3.15	M 24	13 0.51	35 1.38	3 0.12	-	21 0.83	18 0.71	5 0.20	67 2.64	67 2.64	42 1.65	85 3.35	-	19 0.75	12 0.47	17 0.67	20 0.79	30 1.18	-	70 2.76	15 0.59	2 0.08	-

Specification

- Base
Stainless steel AISI 304
Plain, tumbled finish
- Threaded stud / tapped socket
Stainless steel AISI 303
- Inch size hex nut ANSI / ASME B18.2.2
Stainless steel AISI 304
- Metric size hex nut ISO 4032
Stainless steel AISI 304
- Rubber cap
TPE (Santoprene®) ≈ 80 shore A
- Clipped on
- Black
- Rubber pad
NBR (Perbunan®) 70 ±5 shore A
- Vulcanized, non-skid
- Black
- Load Rating Information → page 2121
- Elastomer Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Stud versions T / TK, V / VK and W with Inch thread with certain minimum quantities

Information

GN 43 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the stud / socket versions make these leveling feet universally applicable.

The leveling feet can be screwed to the mounting surface using the mounting hole, which prevents lateral slippage. The base with rubber pad / cap also protects sensitive surfaces.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 42 (Steel, with Mounting Hole) → page 1526
- Leveling Feet GN 42 (Steel, with Slotted Mounting Hole, Rectangular Shape) → page 1526
- Leveling Feet GN 41 (Stainless Steel AISI 304, without Mounting Hole) → page 1520
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Slotted Mounting Hole, Rectangular Shape) → page 1536
- Leveling Feet GN 44 / GN 45 (Stainless Steel AISI 316, with / without Mounting Hole) → page 1524 / 1540
- Threaded Tube Ends EN 448 (Plastic) → page 1578 / 1578
- Threaded Tube Inserts GN 992.5 (Stainless Steel) → page 1581

<p>How to order (Inch)</p> <p style="text-align: center;"> 1 2 3 4 5 GN 43-50-5/16X18-25-D0-X </p>	1 Base diameter d ₁
	2 Thread d ₂
	3 Length l ₇ (Length l ₁)
	4 Type (Base)
	5 Stud / socket version

<p>How to order (Metric)</p> <p style="text-align: center;"> 1 2 3 4 5 GN 43-80-M16-100-D3-V </p>	1 Base diameter d ₁
	2 Thread d ₂
	3 Length l ₂ (Length l ₁ , l ₃ , l ₇)
	4 Type (Base)
	5 Stud / socket version

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

