



Metric table

1			2		Dimensions in: millimeters - inches							
d ₁ Thread			k	d ₂	d ₃ Swivel bore	l ₁	l ₂	l ₃	l ₄	m	Clamping kit for d ₃ Type S	Clamping kit for d ₃ Type K
M 5	M 6	M 8	16 0.63	7 0.28	4.5 0.18	30 1.18	22 0.87	13 0.51	8 0.31	-	GN 511.1-M4-16-S	GN 511.1-M4-16-K
M 6	M 8	-	20 0.79	8.5 0.33	5.5 0.22	38 1.50	28 1.10	17 0.67	10 0.39	14 0.55	GN 511.1-M5-20-S	GN 511.1-M5-20-K
M 8	M 10	-	25 0.98	10 0.39	6.5 0.26	46 1.81	33.5 1.32	20 0.79	12.5 0.49	14 0.55	GN 511.1-M6-25-S	GN 511.1-M6-25-K
M 8	M 10	M 12	30 1.18	10 0.39	6.5 0.26	55 2.17	40 1.57	24 0.94	15 0.59	17 0.67	GN 511.1-M6-30-S	GN 511.1-M6-30-K

Specification

- Aluminum
 - Matte, tumbled finish
 - Black anodized finish
- RoHS compliant



MT
ELS

Accessory

- Clamping kits GN 511.1 → page QVX

Information

GN 484 attachment swivel mounting clamps are primarily designed for mounting GN 479 sensor brackets and GN 479.1 mounting brackets. They are fitted with a central thread and for the size k = 20 mm and higher, an additional hole pattern 4 x M4.

They can be combined with GN 482 swivel mounting clamps and GN 483 T-swivel mounting clamps as well as GN 485 base plate swivel mounting clamps with the same k dimensions to mounting clamp joints. GN 511.1 clamping kits with screw (type S) and adjustable lever (type K) are available for this purpose (part number, see dimensional table).

see also...

- Rods / Tubes GN 480.1 → page QVX
- Sensor Brackets GN 479 → page QVX
- Plain L-Shaped Mounting Brackets GN 479.1 → page QVX

How to order GN 484-M8-20-ELS	1 Thread d ₁
	2 Width k
	3 Finish