



3 Type

- A** Mounting from the back (self-tapping screws)
- B** Mounting from the operator's side

Metric table

b₁	l₁ ±0.25	b₂	d₁	d₂	d₃	h₁	h₂	l₂	l₃ max.	l₄ min.	l₅ max.	l₆	s	RU
12 .47	55 2.17	12.5 .49	M 5	4.3 .17	12.5 .49	40 1.57	34.5 1.36	67.5 2.66	5 .20	14 .55	5 .20	10.5 .41	9 .35	2
12 .47	88 3.46	12.5 .49	M 5	4.3 .17	12.5 .49	40 1.57	34.5 1.36	100.5 3.96	5 .20	14 .55	5 .20	10.5 .41	9 .35	3
12 .47	100 3.94	12.5 .49	M 5	4.3 .17	12.5 .49	40 1.57	34.5 1.36	112.5 4.43	5 .20	14 .55	5 .20	10.5 .41	9 .35	3
12 .47	120 4.72	12.5 .49	M 5	4.3 .17	12.5 .49	40 1.57	34.5 1.36	132.5 5.22	5 .20	14 .55	5 .20	10.5 .41	9 .35	4
12 .47	180 7.09	12.5 .49	M 5	4.3 .17	12.5 .49	40 1.57	34.5 1.36	192.5 7.58	5 .20	14 .55	5 .20	10.5 .41	9 .35	5
12 .47	235 9.25	12.5 .49	M 5	4.3 .17	12.5 .49	40 1.57	34.5 1.36	247.5 9.74	5 .20	14 .55	5 .20	10.5 .41	9 .35	6

Dimensions in: millimeters - inches

Specification

- Tube
Aluminum
- Handle legs
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Tube ELS
Anodized finish, natural color
Handle legs
Black, matte finish
- Tube ESS
Anodized finish, black
Handle legs
Black, matte finish
- Tube ELG
Anodized finish, natural color
Handle legs
Light gray, matte finish
- Socket cap screws DIN 912-M5-45
Steel, zinc plated, black
- Flange nuts DIN 1661-M5
Steel, zinc plated, blue passivated finish
- Self-tapping screws ISO 7049
Steel, zinc plated ST4.8-19
- RoHS compliant

Information

The dimensions of GN 423 rack handles have been designed to accommodate a 19" rack and enclosure layout. The values of the Rack Unit height RU given in the table refer to the height of the equipment, defined as 1U, 2U, 3U, etc.

Tube and handle legs are joined by lightly pressing the legs into the tube, with the result that special lengths are easy to achieve.

Thanks to the included mounting screws, these rack handles can be easily and economically installed.

see also...

- Cabinet "U" Handles GN 425 (Steel)
- Cabinet "U" Handles GN 425 (Aluminum / Stainless Steel)
- Cabinet "U" Handles GN 427 (Aluminum, Ellipse Shaped Profile)
- Cabinet "U" Handles GN 427.5 (Stainless Steel, Ellipse Shaped Profile)

On request

- Special tube lengths other than listed
- Various metric size fasteners and kit packaging

How to order

GN 423-12-120-A-ELS

1	Handle width b₁
2	Length l₁
3	Type
4	Finish